














## GLOVES TECHNICAL DATA

Art.	Picture	Product name	Material	Certificate	Oil resistant	Durability	Grip	Dexterity	Breathability	Application
0899 401 067 0899 401 068 0899 401 069 0899 401 070 0899 401 071		Soffflex	15 g nylon/ spandex liner water based PU + foam nitrile, sandy finish	EN420 EN388:4131	••••	•••	••••	••••	••••	Handling of oily/greasy items, wet items, assembly, flooring, transport, garages, kitchen installation etc.
0899 401 017 0899 401 018 0899 401 019 0899 401 020 0899 401 021		Tigerflex	15 g nylon/lycra liner, foam nitrile coating with nitrile dots	EN420 EN388:4132	••••	••••	•••	••••	••••	Handling of oily/greasy items, dry materials, assembly, roofing, concrete work, repairs, transport, warehouse, plumbing, sanitary work etc.
0899 401 217 0899 401 218 0899 401 219 0899 401 220 0899 401 221		Aquastop	15 Gauge polyester with lycra liner 3/4 double foam nitrile coating	EN420 EN388:4132	••••	••••	•••	•••	••	Handling of oily/greasy items, dry materials, assembly, roofing, concrete work, repairs, transport, warehouse, plumbing, sanitary work etc.
0899 405 027 0899 405 028 0899 405 029 0899 405 030 0899 405 031		Black Mechanic	13 g nylon liner, latex crinkle coating	EN420 EN388:2131	-	••	•••	•••	•	Light to medium duty work, in assembly, onstruct, transport, lumbering, gardening, warehouse, agriculture etc.
0899 400 329 0899 400 330 0899 400 331 0899 400 332		Flexton	13 g grey nylon liner + grey PU coating	EN420 EN388:4131	••	••••	••	•••	•	In electronic industry, packaging, fine assembly, handle small parts in dry and slightly oiled environment.
0899 470 368 0899 470 369 0899 470 370 0899 470 371 0899 470 372 0899 470 373		Black Nitrile Disposable	Powder free, fully textured, chlorinated, 4 mil	EN420 EN374	••••	•	••	••••	-	Automotive industries, laboratory work, food processing, chemical and electrical industries, house painting work, painting and polishing work, cleaning and maintenance work
0899 470 01 0899 470 02 0899 470 03		Blue Nitrile Disposable	Powder free, finger textured, 4 mil	EN420	••••	•	••	••••	-	Painting and polishing work, cleaning and maintenance work, laboratory, chemical and electrical industries.
0899 400 295		General Purpose	Cowsplit, batch palm	EN420	••	•	••	••	••	Light to medium duty work. Assembly, automotive repair, transport, concrete work, agriculture, industry.
0984 310 001		HEAT	10,5" cowsplit leather, lined	EN420 EN388:4144 EN407:413X4X	••	••••	••	•	•	Heat resistant, welding industry
0984 310 002		PRO	16" cowsplit leather, lined	EN420 EN388:4144 EN12477:413X4X	••	••••	••	•	•	Welding industry
0984 310 004		Lefty	16" cowsplit leather, lined, left hand only	EN420 EN388:4144 EN12477:413X4X	••	••••	••	•	•	Welding industry
0899 404 318 0899 404 320		Construct	Knitted glove, with dots	EN420	-	•	•••	••	••	Used in dry areas, form light to medium warehouse work, agriculture, gardening and forestry work etc.
0899 404 321		Basic	Knitted glove, without dots	EN420	-	•	•	••	•••	Used in dry areas, form light to medium warehouse work, agriculture, gardening and forestry work etc.

•••• = Very Good    ••• = Good    •• = General    • = Low    - = Not