












# AKKURUUVINVÄÄNTIMET JA -PORAKONEET / SUORITUSKYKYVERTAILU

	Malli	Tuote n:o	Jännite	Akku	Paino akun kanssa	Max vääntömomentti	Poraus-teho	Terän Ø mm					Max ruuvi Ø mm
								10	20	30	40	50	
	<b>S 12-A</b>	5700 110 2	12V	2.0 Ah	0,8 kg	15/30 Nm	metalli	10					7
							puu	19					
	<b>TBS 12-A</b>	5700 122 2	12V	2.0 Ah	0,8 kg	11 Nm							4
	<b>WB 12-A</b>	5700 107 01	12V		1,1 kg	13 Nm							5
	<b>BS 12-A</b>	5700 111 2	12V	2.0 Ah	0,95 kg	15/30 Nm	metalli	10					7
							puu	19					
	<b>ASS 12-A</b>	5700 106 2	12V	2.0 Ah Li-Ion	1,0 kg	105 Nm							M12
	<b>ASS18-1/2HT</b>	0700 725 5	18 V	5.0 Ah	3,0 kg	610 Nm							M20
	<b>ASS18-A EC Combi</b>	5700 510 2	18V	5.0 Ah	1,8 kg	185 Nm							M16
	<b>BS 18-A Light</b>	5700 504 4	18V	1.5 Ah	1,3 kg	17/38 Nm	metalli	13					8
							puu	38					
	<b>BS 18-A EC Compact</b>	5700 507 2	18V	4.0 Ah	1,7 kg	31/60 Nm	metalli	13					10
							puu	38					
	<b>BS 18-A EC Power</b>	5700 508 2	18V	5.0 Ah Li-Ion	2,2 kg	47/75 Nm	metalli	13					12
							puu	82					
	<b>BS 18-A EC Power Combi</b>	5700 509 2	18V	5.0 Ah Li-Ion	2,3 kg	47/75 Nm	metalli	13					12
							puu	82					
	<b>BS 28-A Combi</b>	0700 647 2	28V	3.0 Ah Li-Ion	3,1 kg	55/90 Nm	metalli	16					10
							alumiini	20					
							puu	50					
							kivi	20					