

▲ 1000 V



Chave de fenda VDE com sextavado interior

Corpo: brunido, isolado.
Força: DIN 911.
Norma: DIN 7439, IEC 900, EN 60900.

				Art. Nr.	
mm	A mm	B/C mm	A inch		
2.5	80	83/27	3 1/8"	613 635 025	1
3.0	80	83/27	3 1/8"	613 635 03	
4.0	80	96/31	3 1/8"	613 635 04	
5.0	80	106/35	3 1/8"	613 635 05	
6.0	100	106/35	4"	613 635 06	
8.0	100	114/38	4"	613 635 08	



Chave de fenda VDE, com fenda AW

Corpo: brunido, isolado.
Norma: IEC 900, EN 60900.

				Art. Nr.	
	A mm	B/C mm	A inch		
AW 20	100	106/35	4"	613 637 20	1
AW 25	100	106/35	4"	613 637 25	



Conjunto de chaves de fenda

para electricistas,
segundo as normas DIN 7437/7438, IEC 900, EN 60900 Art. Nr. 613 963 25

	Art. Nr.		Art. Nr.	
mm				
0.4 x 2.5 x 80	613 631 025	H 1	613 632 1	1
0.8 x 4.0 x 100	613 631 04	H 2	613 632 2	
1.2 x 6.5 x 150	613 631 065			

Art. Nr. 613 963 35



	Art. Nr.		Art. Nr.	
mm				
0.4 x 2.5 x 80	613 631 025	Z 1	613 633 1	1
0.8 x 4.0 x 100	613 631 04	Z 2	613 633 2	
1.2 x 6.5 x 150	613 631 065			