

# Zebra Yatay Tutma Saplı Geçmeli Anahtar

**Yan tarafta vidalama kafası mevcut**

**İç Altı Köşe, küresel başlıklı.**

Şaft: Altı köşeli şaft, yan kafalı, mat kromajlı.

Kafa tipi: SW, DIN 911 gibi

25° açılı vidalama için küresel kafa tipi.

Black Point.



mm	A mm	B/C/D mm	A inç	Art.-Nr.	
5,0	150	35/105/17	6"	0613 130 05	1
6,0	150	35/105/17	6"	0613 130 06	
8,0	150	35/105/17	6"	0613 130 08	
5,0	200	35/105/17	8"	0613 131 05	
6,0	200	35/105/17	8"	0613 131 06	
8,0	200	35/105/17	8"	0613 131 08	
10,0	200	39/117/22	8"	0613 131 10	
12,0	200	39/117/22	8"	0613 131 12	

## İç Altı Köşe

Şaft: Altı köşeli şaft, yan kafalı, mat kromajlı.

Kafa tipi: SW, DIN 911 gibi.

mm	A mm	B/C/D mm	A inç	Art.-Nr.	
2,5	150	27/ 82/13	6"	0613 132 025	1
3,0	150	27/ 82/13	6"	0613 132 03	
4,0	150	27/ 82/13	6"	0613 132 04	
5,0	150	35/105/17	6"	0613 132 05	
6,0	150	35/105/17	6"	0613 132 06	
8,0	150	35/105/17	6"	0613 132 08	
2,5	200	27/ 82/13	8"	0613 133 025	
3,0	200	27/ 82/13	8"	0613 133 03	
4,0	200	27/ 82/13	8"	0613 133 04	
5,0	200	35/105/17	8"	0613 133 05	
6,0	200	35/105/17	8"	0613 133 06	
8,0	200	35/105/17	8"	0613 133 08	
10,0	200	39/117/22	8"	0613 133 10	

## Yatay tutma sapı, iç altı köşe 6 parçalı set

Art.-Nr. 0613 913 06



mm	Şaft uzunluğu mm	Art.-Nr.	
2,5	150	0613 132 025	1
3,0	150	0613 132 03	
4,0	150	0613 132 04	
5,0	150	0613 130 05*	
6,0	150	0613 130 06*	
8,0	150	0613 130 08*	

\* küresel başlıklı.