

ZYLINDERSCHRAUBEN

mit Schlitz
nach DIN 84 (ISO 1207)

Nenn-Ø d	Länge l mm	Messing blank Art.-Nr.	VE/St.	Stahl 4.8 blank Art.-Nr.	VE/St.	Stahl 4.8 vz., blau pass. Art.-Nr.	VE/St.	Stahl 4.8 vz., gelb pass. Art.-Nr.	VE/St.	A2 Art.-Nr.	VE/St.	A4 Art.-Nr.	VE/St.
M 4	32			0040 04 32	2000	0040 4 32	2000	0040 74 32				0289 4 32	
	35	0001 4 35		0040 04 35	1000	0040 4 35	1000/250/100	0040 74 35		0287 4 35	200/500	0289 4 35	
	38		100	0040 04 38	2000	0040 4 38	2000		1000			0289 4 38	
	40	0001 4 40		0040 04 40		0040 4 40	1000/250/100	0040 74 40		0287 4 40		0289 4 40	
	45	0001 4 45	500	0040 04 45		0040 4 45	250/100	0040 74 45		0287 4 45		0289 4 45	
	50	0001 4 50	100	0040 04 50		0040 4 50		0040 74 50		0287 4 50	500	0289 4 50	
	55	0001 4 55	500	0040 04 55		0040 4 55	500	0040 74 55		0287 4 55		0289 4 55	
	60	0001 4 60		0040 04 60	500	0040 4 60	100	0040 74 60	500	0287 4 60		0289 4 60	500
	65			0040 04 65		0040 4 65	500	0040 74 65					
	70			0040 04 70		0040 4 70	100	0040 74 70				0289 4 70	
	75			0040 04 75		0040 4 75	200	0040 74 75	200			0289 4 75	
	80	0001 4 80	200	0040 04 80		0040 4 80	100	0040 74 80	200			0289 4 80	
	85			0040 04 85	200	0040 4 85	200					0289 4 85	
90			0040 04 90		0040 4 90						0289 4 90		
100			0040 04 100		0040 4 100	100	0040 74 100	100					
M 5	5			0040 05 5		0040 5 5	250	0040 75 5					
	6	0001 5 6		0040 05 6	2000	0040 5 6	100/250/1000	0040 75 6		0287 5 6	500	0289 5 6	
	8	0001 5 8	100	0040 05 8		0040 5 8	100/250	0040 75 8	2000	0287 5 8		0289 5 8	
	10	0001 5 10		0040 05 10		0040 5 10	100/250/1000	0040 75 10		0287 5 10		0289 5 10	
	12	0001 5 12		0040 05 12		0040 5 12	1000	0040 75 12	1000	0287 5 12	100/500	0289 5 12	
	14	0001 5 14	1000	0040 05 14		0040 5 14	1000	0040 75 14	200/1000			0289 5 14	
	16	0001 5 16	100	0040 05 16		0040 5 16	100/250/1000	0040 75 16		0287 5 16		0289 5 16	500
	18	0001 5 18	1000	0040 05 18		0040 5 18	100	0040 75 18		0287 5 18	500	0289 5 18	
	20	0001 5 20	100	0040 05 20	1000	0040 5 20	100/250/1000	0040 75 20	1000	0287 5 20	500/100	0289 5 20	
	22	0001 5 22	1000	0040 05 22		0040 5 22	1000	0040 75 22		0287 5 22	500		
	25	0001 5 25		0040 05 25		0040 5 25	100/1000	0040 75 25		0287 5 25		0289 5 25	
	28			0040 05 28		0040 5 28	1000	0040 75 28				0289 5 28	
	30	0001 5 30		0040 05 30		0040 5 30	50/100	0040 75 30		0287 5 30		0289 5 30	
	32		100	0040 05 32		0040 5 32	500				500/100		
	35	0001 5 35		0040 05 35		0040 5 35	100/1000	0040 75 35		0287 5 35		0289 5 35	
	38			0040 05 38		0040 5 38	500					0289 5 38	
	40	0001 5 40		0040 05 40	500	0040 5 40	50/100	0040 75 40	500	0287 5 40		0289 5 40	
	45	0001 5 45	500	0040 05 45		0040 5 45		0040 75 45		0287 5 45	100	0289 5 45	
	50	0001 5 50	100	0040 05 50		0040 5 50		0040 75 50		0287 5 50		0289 5 50	
	55	0001 5 55	500	0040 05 55		0040 5 55		0040 75 55		0287 5 55	500	0289 5 55	200
60	0001 5 60	100	0040 05 60		0040 5 60	100	0040 75 60		0287 5 60	100	0289 5 60		
65	0001 5 65		0040 05 65		0040 5 65		0040 75 65		0287 5 65		0289 5 65		
70	0001 5 70		0040 05 70		0040 5 70		0040 75 70		0287 5 70		0289 5 70		
75			0040 05 75		0040 5 75		0040 75 75			200	0289 5 75		
80	0001 5 80	200	0040 05 80		0040 5 80		0040 75 80	200	0287 5 80		0289 5 80		
85			0040 05 85		0040 5 85		0040 75 85				0289 5 85		
90	0001 5 90	100	0040 05 90		0040 5 90	200	0040 75 90		0287 5 90		0289 5 90		
100	0001 5 100	200	0040 05 100		0040 5 100	100	0040 75 100		0287 5 100	100	0289 5 100		
M 6	6	0001 6 6	1000	0040 06 6		0040 6 6	100/500	0040 76 6					
	8	0001 6 8	1000/500	0040 06 8		0040 6 8	100/500	0040 76 8		0287 6 8	200	0289 6 8	
	10	0001 6 10	100	0040 06 10		0040 6 10	250/100/1000	0040 76 10		0287 6 10		0289 6 10	
	12	0001 6 12		0040 06 12	1000	0040 6 12		0040 76 12	1000	0287 6 12		0289 6 12	
	14	0001 6 14	1000	0040 06 14		0040 6 14	1000	0040 76 14				0289 6 14	
	16	0001 6 16	100	0040 06 16		0040 6 16	250/100/1000	0040 76 16		0287 6 16	100	0289 6 16	
	18	0001 6 18	1000	0040 06 18		0040 6 18	1000	0040 76 18				0289 6 18	
	20	0001 6 20	100	0040 06 20		0040 6 20	250/100/1000	0040 76 20		0287 6 20		0289 6 20	200
	22	0001 6 22	500	0040 06 22		0040 6 22	500	0040 76 22		0287 6 22	200	0289 6 22	
	25	0001 6 25		0040 06 25		0040 6 25	50/250	0040 76 25		0287 6 25		0289 6 25	
	28			0040 06 28		0040 6 28	500	0040 76 28				0289 6 28	
	30	0001 6 30		0040 06 30		0040 6 30	50/250	0040 76 30		0287 6 30		0289 6 30	
	32		100	0040 06 32	500	0040 6 32	500		500		100		
	35	0001 6 35		0040 06 35		0040 6 35	100	0040 76 35		0287 6 35		0289 6 35	
	38			0040 06 38		0040 6 38	500					0289 6 38	
40	0001 6 40		0040 06 40		0040 6 40		0040 76 40		0287 6 40		0289 6 40		
45	0001 6 45	200	0040 06 45		0040 6 45	100	0040 76 45		0287 6 45	200	0289 6 45		
50	0001 6 50	100	0040 06 50	200	0040 6 50	200	0040 76 50	200	0287 6 50	100	0289 6 50	100	