




VDE-SCHRAUBENDREHER



EN 60900, IEC 60900

- Stückprüfung im Wasserbad mit Prüfspannung 10 kV
- Für Arbeiten unter Spannung bis 1.000 Volt (AC), bis 1.500 Volt (DC)
- Kennzeichnung mit dem Herstellungsjahr
- Kälteschlagprüfung bei -40 °C
- (Kennzeichnung C)

 mm				Art.-Nr.	VE/St.
	A mm	B/C mm	A inch		
0,30 x 1,5	40	100/20	1 1/8"	0613 486 015	1
0,30 x 1,8	60	100/20	2 3/8"	0613 486 018	1
0,40 x 2,0	60	100/20	2 3/8"	0613 486 020	1
0,40 x 2,5	75	100/20	3"	0613 486 025	1
0,50 x 3,0	75	100/20	3"	0613 486 030	1

VDE-Schraubendreher Längsschlitz

- Klinge: Rundklinge isoliert, brüniert
- Abtrieb: DIN 5264-A, ISO 2380,
- Norm: EN 60900, IEC 60900

 1000 V








VDE-Schraubendreher Kreuzschlitz (PH)

- Klinge: Rundklinge, isoliert, brüniert
- Abtrieb: ISO 8764-PH
- Norm: EN 60900, IEC 60900

 1000 V



				Art.-Nr.	VE/St.
mm	A mm	B/C mm	A inch		
PH 00	40	100/20	1 1/8"	0613 487 00	1
PH 0	60	100/20	2 3/8"	0613 487 0	1

	Art.-Nr.		Art.-Nr.	VE/St.
mm		mm		
0,30 x 1,5	0613 486 015	PH 00	0613 487 00	1
0,30 x 1,8	0613 486 018	PH 0	0613 487 0	1
0,40 x 2,0	0613 486 020			1
0,40 x 2,5	0613 486 025			1
0,50 x 3,0	0613 486 030			1

Schraubendreher-Satz in Kunststoffkassette

VDE-Schlitz- und Kreuzschlitz-Schraubendreher

Art.-Nr. 0613 489 4

