





KABELVERBINDER, UNISOLIERT

Rundsteckhülsen/Rundstecker

* für Einzelleitungs dichtungen (Seals)

Abbildung	mm ²	Isol.-Ø mm	Seal-Ø mm	Stift-Ø mm	Rastzunge	Werkstoff	Oberfläche	Art.-Nr.	VE St.
	0,5 - 1,0	1,4 - 2,3	3,40	3,5	2 x	CuSn	Sn (verzinnt)	0558 990 001 *	100
	1,5 - 2,5	2,1 - 3,1	3,40	3,5	2 x	CuSn	Sn (verzinnt)	0558 990 002 *	100
	1,5 - 2,5	-	-	3,5	2 x	CuSn	Sn (verzinnt)	0558 990 1	100
	2,1 - 5,3	-	-	3,5	2 x	CuZn	Sn (verzinnt)	0558 997 7	100
	1,5 - 2,5	-	-	3,5	2 x	CuSn	Sn (verzinnt)	0558 990 2	100
	4,0 - 6,0	-	-	3,5	2 x	CuSn	Sn (verzinnt)	0558 990 4	100
	0,5 - 2,0	-	-	3,5	2 x	CuSn	Ag (versilbert)	0558 990 201	100
	1,5 - 2,5	-	-	3,5	2 x	CuSn	Ag (versilbert)	0558 990 203	100
	4,0 - 6,0	-	-	3,5	2 x	CuCrSiTi	Ag (versilbert)	0558 990 204	100

ORSY®-lagerfähig





Ergänzungsprodukte – Empfehlung:

Entriegelungswerkzeug

Art.-Nr. 0713 558 160

Einzelleitungs dichtungen

Art.-Nr. 0558 991 4..

Abbildung	mm ²	Stift-Ø mm	Rastzunge	Werkstoff	Oberfläche	Art.-Nr.	VE/St.
	0,5 - 1,0	2,1	1 x	CuZn	Sn (verzinnt)	0558 996 8	100
	1,0 - 2,5	2,1	1 x	CuZn	Sn (verzinnt)	0558 990 5	100
	1,0 - 2,5	2,1	1 x	CuZn	Sn (verzinnt)	0558 990 6	100
	0,5 - 1,5	2,1	2 x	CuZn	Sn (verzinnt)	0558 993 1	100
	0,5 - 1,5	2,1	2 x	CuZn	Sn (verzinnt)	0558 993 2	100

ORSY®-lagerfähig







Ergänzungsprodukte – Empfehlung:

Entriegelungswerkzeug

Art.-Nr. 0713 558 130

Entriegelungswerkzeug für Art.-Nr. 0558 990 6

Art.-Nr. 0713 558 110

Abbildung	mm ²	Stift-Ø mm	Rastzunge	Werkstoff	Oberfläche	Art.-Nr.	VE/St.
	0,75 - 1,5	1,65	3 x	CuSn	Sn (verzinnt)	0558 996 81	100
	0,75 - 1,5	1,65	3 x	CuSn	Sn (verzinnt)	0558 990 77	100
	0,5 - 1,0	1,65	3 x	CuSn	Sn (verzinnt)	0558 990 8	100
	1,5 - 2,5	1,65	3 x	CuSn	Sn (verzinnt)	0558 996 61	100
	0,5 - 1,0	1,65	3 x	CuSn	Sn (verzinnt)	0558 990 7	100
	0,5 - 1,0	1,65	4 x	CuSn	Sn (verzinnt)	0558 996 4	100
	0,5 - 1,0	1,65	4 x	CuSn	Sn (verzinnt)	0558 997 0	100
	1,5 - 2,5	1,65	4 x	CuSn	Sn (verzinnt)	0558 997 1	100

ORSY®-lagerfähig

Ergänzungsprodukte – Empfehlung:




Entriegelungswerkzeug

Art.-Nr. 0713 558 130

Entriegelungswerkzeug

für Art.-Nr. 0558 990 7/ 0558 990 77/ 0558 996 81

Art.-Nr. 0713 558 140

Abbildung	mm ²	Stift-Ø mm	Werkstoff	Oberfläche	Art.-Nr.	VE/St.
	0,5 - 1,5	4,0	CuZn	Sn (verzinnt)	0558 190 29	100
	0,5 - 1,0	4,0	CuZn	blank	0558 930	100
	1,5 - 2,5	4,0	CuZn	blank	0558 505 1	100
	0,5 - 1,0	4,0	CuZn	blank	0558 503 8	100
	1,5 - 2,5	4,0	CuZn	blank	0558 513 3	100

ORSY®-lagerfähig