

VOLLGEWINDESCHRAUBE ASSY® PLUS VG

ASSY®

Zylinderkopf								Senk- und Senkfrästaschenkopf						
d mm	l mm	lg mm	dh mm	k mm	Antrieb	Art.-Nr. verzinkt, gelb	VE/St.	lg mm	dh mm	k mm	Antrieb	Art.-Nr. verzinkt, blau passiviert	VE/St.	
6,0	80	67	8,2	4,7	AW® 30	0165 36 80	100	67	12,0	4,2	AW® 30	0165 46 80	100	
	100	87				0165 36 100		87				0165 46 100		
	120	107				0165 36 120		107				0165 46 120		
	140	123				0165 36 140		123				0165 46 140		
	160	143				0165 36 160		143				0165 46 160		
	180	163				0165 36 180		163				0165 46 180		
	200	183				0165 36 200		183				0165 46 200		
	220	203				0165 36 220								
	240	223				0165 36 240								
	260	243				0165 36 260								
8,0	120	101	10,0	7,5	AW® 40	0165 38 120	50	101	15,0	Senkfrästaschenkopf k = 4,6mm	AW® 40	0165 48 120	75	
	140	121				0165 38 140		121				0165 48 140		
	160	141				0165 38 160		141				0165 48 160		
	180	161				0165 38 180		161				0165 48 180		
	200	181				0165 38 200	75	181				0165 48 200		
	220	201				0165 38 220		201				0165 48 220		
	240	221				0165 38 240		221				0165 48 240		
	260	241				0165 38 260		241				0165 48 260		
	280	261				0165 38 280	50	261				0165 48 280		
	300	275				0165 38 300		275				0165 48 300		
	330	305				0165 38 330		305				0165 48 330		
	380	355				0165 38 380		355				0165 48 380		
	430	405				0165 38 430	25	405				0165 48 430		
	480	445				0165 38 480		445				0165 48 480		
	530	495				0165 38 530		495				0165 48 530		
	580	545				0165 38 580		545				0165 48 580		
10,0	120	97	13,5	8,0	AW® 50	0165 310 120	50	97	20,0	Senkkopf k = 5,5mm	AW® 50	0165 410 120	50	
	140	117				0165 310 140		117				0165 410 140		
	160	137				0165 310 160		137				0165 410 160		
	180	157				0165 310 180		157				0165 410 180		
	200	177				0165 310 200		177				0165 410 200		
	220	197				0165 310 220		197				0165 410 220		
	240	217				0165 310 240		217				0165 410 240		
	260	237				0165 310 260		237				0165 410 260		
	280	257				0165 310 280		257				0165 410 280		
	300	272				0165 310 300		272				0165 410 300		
	320	292				0165 310 320	292	0165 410 320						
	340	312				0165 310 340	312	0165 410 340						
	360	332				0165 310 360	332	0165 410 360						
	380	352				0165 310 380	352	0165 410 380						
	400	372				0165 310 400	372	0165 410 400						
	430	402				0165 310 430	25	402				0165 410 430		
	480	442				0165 310 480		442				0165 410 480		
	530	492				0165 310 530		492				0165 410 530		
	580	542				0165 310 580		542				0165 410 580		
	600							562				0165 410 600		
650	612	0165 310 650	612	0165 410 650										