



INFORMATION SÄBELSÄGEBLÄTTER

| Material | Qualität | Art.-Nr. | VE/St. | |  |  |  |
|----------|----------|---------------|--------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| | | | | | Zahnteilung mm und inch | Länge total mm und inch | Dicke mm |
| Metall | *** | 0615 922 826 | 1=5 |  | 1,8/2,6 10/14 tpi | 228 9" | 0,9 |
| | | 0615 930 526 | 1=5 |  | 1,8/2,6 10/14 tpi | 305 12" | 0,9 |
| | | 0615 910 010 | 1=5 |  | 1,0 24 tpi | 100 4" | 0,9 |
| Inox | *** | 0615 911 614 | 1=3 |  | 1,4 18 tpi | 116,5 4,5" | 1,25 |
| Metall | ** | 0608 030 31 * | 1=5 |  | 1,8 18 tpi | 200 8" | 1,6 |
| | | 0608 030 32 * | 1=5 |  | 1,8 12 tpi | 150 6" | 1,6 |
| | | 0608 030 35 * | 1=5 |  | 3,2 9 tpi | 140 6" | 1,6 |
| | | 0608 030 36 * | 1=5 |  | 3,2 9 tpi | 200 8" | 1,6 |

* passend für Würth RS 4, TS 1 und Roller-Rems Maschine.