

KESSELBAUSCHRAUBE

Gew.-Ø	Länge	Stahl verzinkt, blau passiviert (A2K)				Stahl blank			
		ISO 4017 Vollgewinde		ISO 4014 mit Schaft		ISO 4017 Vollgewinde		ISO 4014 mit Schaft	
		Art.-Nr.	VE/St.	Art.-Nr.	VE/St.	Art.-Nr.	VE/St.	Art.-Nr.	VE/St.
M24	90	0065 024 90	10	0065 924 90	10	0065 724 90	10	0065 824 90	10
M24	95			0065 924 95	10				
M24	100			0065 924 100	10	0065 724 100	10	0065 824 100	10
M24	110			0065 924 110	10			0065 824 110	10
M24	120			0065 924 120	10	0065 724 120	10	0065 824 120	10
M24	130			0065 924 130	10			0065 824 130	10
M24	140			0065 924 140	10			0065 824 140	10
M24	150			0065 924 150	10	0065 724 150	10	0065 824 150	10
M24	160			0065 924 160	10	0065 724 160	10	0065 824 160	10
M24	170			0065 924 170	10			0065 824 170	10
M24	180			0065 924 180	10			0065 824 180	10
M24	190							0065 824 190	10
M24	200							0065 824 200	10
M24	210			0065 924 210	10				
M24	220			0065 924 220	10			0065 824 220	10
M27	60					0065 727 60	10		
M27	70	0065 027 70	10			0065 727 70	10		
M27	80	0065 027 80	10	0065 927 80	10	0065 727 80	10	0065 827 80	10
M27	90	0065 027 90	10	0065 927 90	10	0065 727 90	10	0065 827 90	10
M27	95			0065 927 95	10				
M27	100			0065 927 100	10			0065 827 100	10
M27	110	0065 027 110	10	0065 927 110	10	0065 727 110	10	0065 827 110	10
M27	120			0065 927 120	10	0065 727 120	10	0065 827 120	10
M27	130			0065 927 130	10			0065 827 130	10
M27	140			0065 927 140	10			0065 827 140	10
M27	150			0065 927 150	10			0065 827 150	10
M27	160			0065 927 160	5			0065 827 160	10
M27	180			0065 927 180	5			0065 827 180	10
M27	200			0065 927 200	5				
M30	80					0065 730 80	5	0065 830 80	10
M30	90							0065 830 90	10
M30	100			0065 930 100	5	0065 730 100	5		
M30	110			0065 930 110	5			0065 830 110	10
M30	120			0065 930 120	5			0065 830 120	10
M30	130			0065 930 130	5	0065 730 130	5	0065 830 130	10
M30	140			0065 930 140	5			0065 830 140	10
M30	150			0065 930 150	5				
M30	160			0065 930 160	5			0065 830 160	10
M30	180			0065 930 180	5				
M30	200			0065 930 200	5			0065 830 200	10
M30	220			0065 930 220	5			0065 830 220	5
M30	240			0065 930 240	5				
M33	110	0065 033 110	5						
M33	130	0065 033 130	5						

ORSY®-lagerfähig