

FLACHRUNDSCHRAUBE

mit Vierkantansatz (Schlossschrauben)
DIN 603 (ISO 8677)

Nenn- \varnothing	Länge l mm	Stahl 4.8 blank mit Mutter Art.-Nr.	VE/St.	Stahl 4.8, vz. blau passiviert mit Mutter Art.-Nr.	VE/St.	Stahl 8.8, vz. blau passi- viert o. Mutter Art.-Nr.	VE/St.	A2 o. Mutter Art.-Nr.	VE/St.	A4 o. Mutter Art.-Nr.	VE/St.
M16	420	0223 016 420	10								
M16	440			0223 16 440	10						
M16	460			0223 16 460	10						
M20	70			0223 20 70	10						
M20	80	0223 020 80	25	0223 20 80	25						
M20	90	0223 020 90	25								
M20	100	0223 020 100	25	0223 20 100	25						
M20	110	0223 020 110	25	0223 20 110	25						
M20	120	0223 020 120	25	0223 20 120	25						
M20	130	0223 020 130	25	0223 20 130	25						
M20	140	0223 020 140	25	0223 20 140	25						
M20	150	0223 020 150	25	0223 20 150	25						
M20	160	0223 020 160	25	0223 20 160	25						
M20	180	0223 020 180	25	0223 20 180	25						
M20	200	0223 020 200	25	0223 20 200	25						
M20	220	0223 020 220	25	0223 20 220	25						
M20	240	0223 020 240	25	0223 20 240	25						
M20	260	0223 020 260	25	0223 20 260	25						
M20	280	0223 020 280	25	0223 20 280	25						
M20	300	0223 020 300	25	0223 20 300	25						

ORSY[®]-lagerfähig