

# WÜPLAST® W 1452

Nenn-Ø d mm	Länge l mm	Stahl 10.9 A3K Art.-Nr.	VE St.	Stahl 10.9 P3E** Art.-Nr.	VE St.	Stahl 10.9 P3R** Art.-Nr.	VE St.	A2 Art.-Nr.	VE St.
4	20	<b>42284 20</b>	1000/ 2000	<b>42294 20</b>	2000	<b>42304 20</b>	2000		2000
	25	<b>42284 25</b>	500/ 1000	<b>42294 25</b>	1000	<b>42304 25</b>	1000		
	30	<b>42284 30</b>							
	35	<b>42284 35</b>							
	40	<b>42284 40</b>							
5	10	<b>42285 10</b>	500/ 1000	<b>42295 10</b>	1000	<b>42305 10</b>	1000	<b>42315 10</b>	1000
	12	<b>42285 12</b>		<b>42295 12</b>		<b>42305 12</b>		<b>42315 12</b>	
	16	<b>42285 16</b>		<b>42295 16</b>	<b>42305 16</b>				
	20	<b>42285 20</b>		<b>42295 20</b>	<b>42305 20</b>				
	25	<b>42285 25</b>		<b>42295 25</b>	<b>42305 25</b>				
	30	<b>42285 30</b>							
	35	<b>42285 35</b>							
	40	<b>42285 40</b>							
6	20	<b>42286 20</b>	500/ 1000						
	25	<b>42286 25</b>							
	30	<b>42286 30</b>							

\*\* Lieferzeiten auf Anfrage