







MASCHINENGEWINDEBOHRER HSCO MULTI SPEZIAL DURCHGANGSLOCH DIN 376

Art.-Nr.	0659 760 300	0659 760 400	0659 760 500	0659 760 600	0659 760 800	0659 761 000
VE	1/10	1/10	1/10	1/10	1/10	1/5
Farbleitsystem	 Edelstahl; Stahl; NE-Metall	 Edelstahl; Stahl; NE-Metall	 Edelstahl; Stahl; NE-Metall	 Edelstahl; Stahl; NE-Metall	 Edelstahl; Stahl; NE-Metall	 Edelstahl; Stahl; NE-Metall
Gewindeart x Nenndurchmesser	M3	M4	M5	M6	M8	M10
Steigung	0,5 mm	0,7 mm	0,8 mm	1 mm	1,25 mm	1,5 mm
Länge	56 mm	63 mm	70 mm	80 mm	90 mm	100 mm
Schaftdurchmesser	2,2 mm	2,8 mm	3,5 mm	4,5 mm	6 mm	7 mm
Größe Vierkant	1,8 mm	2,1 mm	2,7 mm	3,4 mm	4,9 mm	5,5 mm
Kernlochdurchmesser	2,5 mm	3,3 mm	4,2 mm	5 mm	6,8 mm	8,5 mm