



## Complete Set

**M 5 / M 6 / M 8 / M 10 / M 12**

- Metric coarse thread
- Bushes and tools for 5 sizes with 2 different lengths of bushes

**Art. No. 0964 961 7**

Thread Ø x pitch x length, mm		
M 5 x 0.8 x 7.6	M 8 x 1.25 x 16.2	5
M 5 x 0.8 x 10.0	M 10 x 1.5 x 14.0	
M 6 x 1.0 x 9.4	M 10 x 1.5 x 20.0	
M 6 x 1.0 x 12.0	M 12 x 1.75 x 16.2	
M 8 x 1.25 x 11.7	M 12 x 1.75 x 24.0	



## Complete Set

**M 6 / M 8 / M 10**

- Metric coarse thread
- Bushes and tools for 3 sizes with 2 different lengths of bushes each

**Art. No. 0964 961 6**

Thread Ø x pitch x length, mm		
M 6 x 1.0 x 9.4	M 8 x 1.25 x 16.2	5
M 6 x 1.0 x 12.0	M 10 x 1.5 x 14.0	
M 8 x 1.25 x 11.7	M 10 x 1.5 x 20.0	

## Bush Refill Packs

**Type: steel, galvanized, passivated and A2 with contents of 25 each**

Metric coarse thread
Metric fine thread

Thread Ø x pitch x length, mm	Art. No. Steel galvanized
M 4 x 0.7 x 6.0	<b>0663 4 60*</b>
M 4 x 0.7 x 8.0	<b>0663 4 80*</b>
M 5 x 0.8 x 7.6	<b>0663 5 76</b>
M 5 x 0.8 x 10.0	<b>0663 5 100</b>
M 6 x 1 x 9.4	<b>0663 6 94</b>
M 6 x 1 x 12.0	<b>0663 6 120</b>
M 7 x 1 x 10.0	<b>0663 7 100</b>
M 7 x 1 x 14.0	<b>0663 7 140</b>
M 8 x 1 x 11.7	<b>0663 8 117</b>
M 8 x 1.25 x 11.7	<b>0663 812 511</b>
M 8 x 1.25 x 16.2	<b>0663 812 516</b>
M 9 x 1.25 x 13.0	<b>0663 912 513</b>
M 9 x 1.25 x 18.0	<b>0663 912 518</b>
M 10 x 1 x 6.2	<b>0663 101</b>
M 10 x 1 x 9.0	<b>0663 101 90*</b>
M 10 x 1 x 15.0	<b>0663 10 150</b>
M 10 x 1.25 x 9.0	<b>0663 101 250*</b>
M 10 x 1.25 x 15.0	<b>0663 101 251</b>
M 10 x 1.25 x 20.0	<b>0663 101 252</b>
M 10 x 1.5 x 14.0	<b>0663 101 514</b>
M 10 x 1.5 x 20.0	<b>0663 101 520</b>
M 11 x 1.25 x 22.0	<b>0663 111 122*</b>

Thread Ø x pitch x length, mm	Art. No. Steel galvanized
M 11 x 1.5 x 16.0	<b>0663 111 516*</b>
M 11 x 1.5 x 22.0	<b>0663 111 522*</b>
M 12 x 1.5 x 6.7	<b>0663 121 567</b>
M 12 x 1.5 x 9.3	<b>0663 121 593</b>
M 12 x 1.5 x 16.3	<b>0663 121 516</b>
M 12 x 1.5 x 24.0	<b>0663 121 524</b>
M 12 x 1.75 x 16.2	<b>0663 121 751</b>
M 12 x 1.75 x 24.0	<b>0663 121 752</b>
M 14 x 1.5 x 6.5	<b>0663 141 565</b>
M 14 x 1.5 x 9.3	<b>0663 141 593</b>
M 14 x 1.5 x 12.8	<b>0663 141 512</b>
M 14 x 1.5 x 16.0	<b>0663 141 516</b>
M 14 x 1.5 x 26.0	<b>0663 141 526</b>
M 16 x 1.5 x 7.0	<b>0663 161 570*</b>
M 16 x 1.5 x 12.7	<b>0663 161 512*</b>
M 16 x 1.5 x 24.0	<b>0663 161 524*</b>
M 16 x 2 x 24.0	<b>0663 16 240*</b>
M 16 x 2 x 32.0	<b>0663 16 320*</b>
M 18 x 1.5 x 10.0	<b>0663 181 610*</b>
M 18 x 1.5 x 18.3	<b>0663 181 518*</b>
M 18 x 1.5 x 27.0	<b>0663 181 527*</b>

Thread Ø x pitch x length, mm	Art. No. A2
M 6 x 1 x 9.4	<b>0663 06 94*</b>
M 6 x 1 x 12.0	<b>0663 06 120*</b>
M 8 x 1.25 x 11.7	<b>0663 081 211*</b>
M 8 x 1.25 x 16.2	<b>0663 081 216*</b>
M 10 x 1.5 x 14.0	<b>0663 011 514*</b>
M 10 x 1.5 x 20.0	<b>0663 011 520*</b>



\* ORSY