

FILLISTER-HEAD SCREWS

DIN 6912 with low Allen head
and key guide

Nominal diameter d	Length l in mm	Bare 08.8 steel Art. No.	P. Qty.	08.8 steel, galv., blue passivated Art. No.	P. Qty.	A2 Art. No.	P. Qty.	A4 Art. No.	P. Qty.
M6	45	0088 6 45	200	0086 6 45	100	0098 6 45	200	0099 6 45	200
M6	50	0088 6 50	200	0086 6 50	200	0098 6 50	200	0099 6 50	100
M6	55	0088 6 55	200	0086 6 55	200	0098 6 55	100	0099 6 55	100
M6	60	0088 6 60	200	0086 6 60	200	0098 6 60	100	0099 6 60	100
M6	65	0088 6 65	200			0098 6 65	100		
M6	70	0088 6 70	200	0086 6 70	100	0098 6 70	100	0099 6 70	100
M6	75			0086 6 75	200				
M6	80	0088 6 80	100	0086 6 80	200	0098 6 80	100	0099 6 80	100
M6	85			0086 6 85	100				
M6	90	0088 6 90	100	0086 6 90	100	0098 6 90	200		
M6	100	0088 6 100	200	0086 6 100	100				
M6	110	0088 6 110	100	0086 6 110	100	0098 6 110	50		
M6	120	0088 6 120	100	0086 6 120	100				
M6	125								
M6	140	0088 6 140	100	0086 6 140	200				
M8	8			0086 8 8	21				
M8	10	0088 8 10	100	0086 8 10	200	0098 8 10	200		
M8	12	0088 8 12	100	0086 8 12	100	0098 8 12	100	0099 8 12	200
M8	13	0088 8 13	100						
M8	14			0086 8 14	200	0098 8 14	200	0099 8 14	200
M8	16	0088 8 16	200	0086 8 16	200	0098 8 16	100	0099 8 16	200
M8	17			0086 8 17	50				
M8	18	0088 8 18	200	0086 8 18	200				
M8	20	0088 8 20	200	0086 8 20	200	0098 8 20	100	0099 8 20	200
M8	22	0088 8 22	200						
M8	25	0088 8 25	200	0086 8 25	200	0098 8 25	100	0099 8 25	200
M8	30	0088 8 30	200	0086 8 30	200	0098 8 30	100	0099 8 30	200
M8	35	0088 8 35	200	0086 8 35	200	0098 8 35	100	0099 8 35	200
M8	40	0088 8 40	200	0086 8 40	200	0098 8 40	100	0099 8 40	200
M8	45	0088 8 45	100	0086 8 45	100	0098 9 45	100	0099 8 45	200
M8	50	0088 8 50	200	0086 8 50	200	0098 8 50	100	0099 8 50	100
M8	55	0088 8 55	200	0086 8 55	200	0098 8 55	100		
M8	60	0088 8 60	200	0086 8 60	200	0098 8 60	100	0099 8 60	100
M8	65	0088 8 65	200	0086 8 65	200	0098 8 65	100		
M8	70	0088 8 70	100	0086 8 70	200	0098 8 70	100	0099 8 70	100
M8	75	0088 8 75	100	0086 8 75	200	0098 8 75	100		
M8	80	0088 8 80	100	0086 8 80	200	0098 8 80	100	0099 8 80	100
M8	85	0088 8 85	100	0086 8 85	100				
M8	90	0088 8 90	100	0086 8 90	50	0098 8 90	50	0099 8 90	100
M8	100	0088 8 100	100	0086 8 100	50	0098 8 100	100		
M8	110	0088 8 110	100	0086 8 110	100	0098 8 110	25		
M8	120			0086 8 120	50				
M8	130			0086 8 130	100				
M8	150			0086 8 150	100				
M10	12			0086 10 12	200				
M10	14	0088 10 14	200						
M10	16	0088 10 16	200	0086 10 16	200	0098 10 16	100	0099 10 16	100
M10	18	0088 10 18	200						
M10	20	0088 10 20	200	0086 10 20	200	0098 10 20	100	0099 10 20	100
M10	22			0086 10 22	200				
M10	25	0088 10 25	200	0086 10 25	200	0098 10 25	100	0099 10 25	100
M10	30	0088 10 30	200	0086 10 30	200	0098 10 30	100	0099 10 30	100
M10	35	0088 10 35	100	0086 10 35	100	0098 10 35	100	0099 10 35	100
M10	40	0088 10 40	100	0086 10 40	100	0098 10 40	100	0099 10 40	100
M10	45	0088 10 45	100	0086 10 45	100	0098 10 45	100	0099 10 45	100
M10	50	0088 10 50	100	0086 10 50	100	0098 10 50	100	0099 10 50	50
M10	55	0088 10 55	100	0086 10 55	200	0098 10 55	100		
M10	60	0088 10 60	100	0086 10 60	100	0098 10 60	50	0099 10 60	50
M10	65	0088 10 65	100	0086 10 65	100	0098 10 65	100		
M10	70	0088 10 70	100	0086 10 70	100	0098 10 70	50		
M10	80	0088 10 80	100	0086 10 80	100	0098 10 80	50		
M10	85	0088 10 85	100	0086 10 85	100				
M10	90	0088 10 90	100	0086 10 90	100	0098 10 90	50		
M10	100	0088 10 100	100	0086 10 100	25	0098 10 100	50		
M10	110	0088 10 110	50	0086 10 110	50				
M10	120	0088 10 120	50	0086 10 120	25				
M10	130	0088 10 130	50	0086 10 130	50	0098 10 130	50		
M10	140	0088 10 140	25	0086 10 140	50	0098 10 140	10		
M10	150	0088 10 150	50	0086 10 150	50				