



Shim Rings

DIN 988

bare steel

d in mm	d ₁ in mm	s in mm	Bare steel Art. No.	P. Qty.
5	10	0.3	0425 051 003	100
6	12	0.1	0425 061 201	50
		0.2	0425 061 202	
		0.3	0425 061 203	100
		0.5	0425 061 205	
		1.0	0425 061 210	
8	14	0.1	0425 081 401	50
		0.2	0425 081 402	
		0.3	0425 081 403	100
		0.5	0425 081 405	
		1.0	0425 081 410	
10	16	0.1	0425 101 601	50
		0.2	0425 101 602	
		0.3	0425 101 603	100
		0.5	0425 101 605	
		1.0	0425 101 610	
12	18	0.1	0425 121 801	50
		0.2	0425 121 802	
		0.3	0425 121 803	100
		0.5	0425 121 805	
		1.0	0425 121 810	
14	20	0.1	0425 142 001	50
		0.2	0425 142 002	
		0.3	0425 142 003	100
		0.5	0425 142 005	
		1.0	0425 142 010	
16	22	0.1	0425 162 201	50
		0.2	0425 162 202	
		0.3	0425 162 203	100
		0.5	0425 162 205	
		1.0	0425 162 210	
18	25	0.1	0425 182 501	50
		0.2	0425 182 502	
		0.3	0425 182 503	100
		0.5	0425 182 505	
		1.0	0425 182 510	
20	28	0.1	0425 202 801	50
		0.2	0425 202 802	
		0.3	0425 202 803	100
		0.5	0425 202 805	
		1.0	0425 202 810	
25	35	0.1	0425 253 501	50
		0.2	0425 253 502	
		0.3	0425 253 503	100
		0.5	0425 253 505	
		1.0	0425 253 510	
28	40	0.1	0425 284 001	50
		0.2	0425 284 002	
		0.3	0425 284 003	100
		0.5	0425 284 005	
		1.0	0425 284 010	

d in mm	d ₁ in mm	s in mm	Bare steel Art. No.	P. Qty.
30	42	0.1	0425 304 201	50
		0.2	0425 304 202	
		0.3	0425 304 203	100
		0.5	0425 304 205	
		1.0	0425 304 210	
32	45	0.1	0425 324 501	50
		0.2	0425 324 502	
		0.3	0425 324 503	100
		0.5	0425 324 505	
		1.0	0425 324 510	
35	45	0.1	0425 354 501	50
		0.2	0425 354 502	
		0.3	0425 354 503	100
		0.5	0425 354 505	
		1.0	0425 354 510	
40	50	0.1	0425 405 001	50
		0.2	0425 405 002	
		0.3	0425 405 003	100
		0.5	0425 405 005	
		1.0	0425 405 010	
42	52	0.1	0425 425 201	50
		0.2	0425 425 202	
		0.3	0425 425 203	100
		0.5	0425 425 205	
		1.0	0425 425 210	
45	55	0.1	0425 455 501	50
		0.2	0425 455 502	
		0.3	0425 455 503	50/250
		0.5	0425 455 505	
		1.0	0425 455 510	
50	62	0.1	0425 506 201	50
		0.2	0425 506 202	
		0.3	0425 506 203	50
		0.5	0425 506 205	
		1.0	0425 506 210	
52	65	0.5	0425 526 505	50
		1.0	0425 526 510	
55	68	0.5	0425 556 805	50
		1.0	0425 556 810	
56	70	1.0	0425 567 010	50
		0.1	0425 567 201	
		0.2	0425 567 202	
		0.3	0425 567 203	
		0.5	0425 567 205	
56	72	1.0	0425 567 210	100/250
		0.1	0425 567 201	
		0.2	0425 567 202	
		0.3	0425 567 203	
		0.5	0425 567 205	
60	75	0.5	0425 607 505	50
		1.0	0425 607 510	
		1.0	0425 607 510	