



Cotter Pins

DIN 94 (ISO 1234)

Galvanized steel,
blue passivated
A2
A4



- For securing castellated nuts in conjunction with bolts or threaded pins with cotter pin hole (e.g. steering and tracking gears in motor vehicles).
- For securing cotter bolts.

Ordering example

Galvanized, dia. 2.0 x L 25 mm
Art. No. 0470 2 x 259.
A2 Art. No. 0474

Assortment



Cotter pin assortment DIN 94,
galvanized, blue passivated
Contents: 12 dimensions
from 1.6 x 20 to 6.3 x 63 = 1525 pcs.
Art. No. 0964 470

Dia. d in mm	l in mm	a in mm	b in mm	c in mm	Galv. steel, blue pass. Art. No.	P. Qty.	
1	16	1.6	3	1.6	0470 1 16	500	
1	20	1.6	3	1.6	0470 1 20		
1	25	1.6	3	1.6	0470 1 25		
1	32	1.6	3	1.6	0470 1 32	1000	
1.6	14	2.5	3.2	2.4	0470 16 14	500	
1.6	16	2.5	3.2	2.4	0470 16 16		
1.6	20	2.5	3.2	2.4	0470 16 20		
1.6	25	2.5	3.2	2.4	0470 16 25		
1.6	32	2.5	3.2	2.4	0470 16 32		
1.6	36	2.5	3.2	2.4	0470 16 36		
2	10	2.5	4	3.2	0470 2 10	100	
2	12	2.5	4	3.2	0470 2 12	500	
2	14	2.5	4	3.2	0470 2 14		
2	16	2.5	4	3.2	0470 2 16		
2	18	2.5	4	3.2	0470 2 18		
2	20	2.5	4	3.2	0470 2 20	1000	
2	22	2.5	4	3.2	0470 2 22		
2	25	2.5	4	3.2	0470 2 25		
2	32	2.5	4	3.2	0470 2 32		
2	36	2.5	4	3.2	0470 2 36		
2	40	2.5	4	3.2	0470 2 40		
2.5	20	2.5	5	4	0470 25 20	250	
2.5	22	2.5	5	4	0470 25 22	500	
2.5	25	2.5	5	4	0470 25 25	500/1000	
2.5	32	2.5	5	4	0470 25 32	500	
2.5	36	2.5	5	4	0470 25 36	500	
2.5	40	2.5	5	4	0470 25 40	500/1000	
2.5	45	2.5	5	4	0470 25 45	500	
3.2	12	2.5	5	4	0470 32 12	1000	
3.2	16	2.5	5	4	0470 32 16	500	
3.2	18	2.5	5	4	0470 32 18		
3.2	20	2.5	5	4	0470 32 20		
3.2	22	2.5	5	4	0470 32 22		
3.2	25	2.5	5	4	0470 32 25		250/500
3.2	28	2.5	5	4	0470 32 28		50
3.2	32	2.5	5	4	0470 32 32	250/500	
3.2	36	2.5	5	4	0470 32 36	500	
3.2	40	2.5	5	4	0470 32 40	250/500	
3.2	45	2.5	5	4	0470 32 45	500	
3.2	50	2.5	5	4	0470 32 50		
3.2	63	2.5	5	4	0470 32 63		
3.5	30	4	7.2	5.9	0470 35 30		500
3.5	35	4	7.2	5.9	0470 35 35		250/500
3.5	40	4	7.2	5.9	0470 35 40		500
3.5	45	4	7.2	5.9	0470 35 45	500	
3.5	50	4	7.2	5.9	0470 35 50	250	
3.5	60	4	7.2	5.9	0470 35 60	250	
4	20	4	8	6.5	0470 4 20		
4	25	4	8	6.5	0470 4 25		
4	28	4	8	6.5	0470 4 28		
4	32	4	8	6.5	0470 4 32		
4	36	4	8	6.5	0470 4 36		
4	40	4	8	6.5	0470 4 40	500	
4	45	4	8	6.5	0470 4 45	250	

Dia. d in mm	l in mm	a in mm	b in mm	c in mm	Galv. steel, blue pass. Art. No.	P. Qty.	
4	50	4	8	6.5	0470 4 50	250	
4	56	4	8	6.5	0470 4 56		
4	63	4	8	6.5	0470 4 63		
4	71	4	8	6.5	0470 4 71		
4	80	4	8	6.5	0470 4 80		
4.5	40	4	8	6.5	0470 45 40		
4.5	45	4	8	6.5	0470 45 45	250	
4.5	50	4	8	6.5	0470 45 50		
4.5	63	4	8	6.5	0470 45 63		
4.5	70	4	8	6.5	0470 45 70		
5	20	4	10	8	0470 5 20		250
5	22	4	10	8	0470 5 22		100
5	25	4	10	8	0470 5 25		
5	28	4	10	8	0470 5 28		
5	32	4	10	8	0470 5 32		
5	36	4	10	8	0470 5 36	250	
5	40	4	10	8	0470 5 40		
5	45	4	10	8	0470 5 45		
5	50	4	10	8	0470 5 50		
5	56	4	10	8	0470 5 56		100/250
5	63	4	10	8	0470 5 63		100
5	71	4	10	8	0470 5 71	100	
5	80	4	10	8	0470 5 80		
5.5	50	4	10	8	0470 55 50		
5.5	55	4	10	8	0470 55 55		100
5.5	60	4	10	8	0470 55 60		250
6.3	32	4	12.6	10.3	0470 63 32		
6.3	36	4	12.6	10.3	0470 63 36	100/250	
6.3	40	4	12.6	10.3	0470 63 40	100	
6.3	45	4	12.6	10.3	0470 63 45	1000	
6.3	50	4	12.6	10.3	0470 63 50	100	
6.3	63	4	12.6	10.3	0470 63 63		
6.3	71	4	12.6	10.3	0470 63 71		
6.3	80	4	12.6	10.3	0470 63 80		
7	80				0470 7 80		50
8	40	4	16	13.1	0470 8 40		100
8	50	4	16	13.1	0470 8 50		
8	56	4	16	13.1	0470 8 56		
8	63	4	16	13.1	0470 8 63		
8	71	4	16	13.1	0470 8 71	50	
8	80	4	16	13.1	0470 8 80		
8	90	4	16	13.1	0470 8 90		
8	100	4	16	13.1	0470 8 100		
8	112	4	16	13.1	0470 8 112		
8	125	4	16	13.1	0470 8 125		100
8	140	4	16	13.1	0470 8 140		
10	56	6.3	20	16.6	0470 10 56		
10	63	6.3	20	16.6	0470 10 63	250	
10	71	6.3	20	16.6	0470 10 71		
10	80	6.3	20	16.6	0470 10 80		
10	90	6.3	20	16.6	0470 10 90		
10	100	6.3	20	16.6	0470 10 100		50
10	125	6.3	20	16.6	0470 10 125		
10	140	6.3	20	16.6	0470 10 140		