











# ASSY® 3.0

# ASSY®


Dia. d in mm			l in mm	lg in mm	Bit color	dh in mm	   				dh in mm	  			dh in mm	lg in mm	 		P. Qty.
Art. No.	Art. No.	Art. No.	Art. No.	Art. No.			Art. No.	Art. No.	Art. No.	Art. No.		Art. No.							
5.0	16	11	AW®20	9.5	0170 050 16									14.0	0153 050 016	500			
	17				0170 050 20		0170 250 20							15.0	0153 050 017				
	20	15			0170 050 25		0170 250 25							18.0	0153 050 020				
	25	20			0170 050 30		0170 250 30							22.0	0153 050 025				
	30	25				0170 150 30		0170 350 30						27.0	0153 050 030				
		20																	
	35	30			0170 050 35		0170 250 35			0154 050 35					32.0		0153 050 035		
		20				0170 150 35		0170 350 35											
	40	32			0170 050 40		0170 250 40			0154 050 40		0154 350 40			37.0		0153 050 040		
		25				0170 150 40		0170 350 40											
	45	37			0170 050 45		0170 250 45								42.0		0153 050 045		
		30				0170 150 45		0170 350 45											
	50	42			0170 050 50		0170 250 50			0154 050 50		0154 350 50			46.0		0153 050 050		
		30				0170 150 50		0170 350 50											
	55	47			0170 050 55		0170 250 55								52.0		0153 050 055		
		32				0170 150 55		0170 350 55											
	60	52			0170 050 60		0170 250 60			0154 050 60	0154 250 60	0154 350 60			56.0		0153 050 060		
		37				0170 150 60		0170 350 60			0154 250 70	0154 350 70			66.0		0153 050 070		
70	62	0170 050 70		0170 250 70															
	42		0170 150 70		0170 350 70														
80	72	0170 050 80		0170 250 80				0154 250 80	0154 350 80										
	42		0170 150 80		0170 350 80							42.0	0153 150 080						
90	47		0170 150 90		0170 350 90							46.0	0153 150 090						
100	52		0170 150 100		0170 350 100							52.0	0153 150 100						
110	52		0170 150 110		0170 350 110														
120	62		0170 150 120		0170 350 120														
6.0	30	24	AW® 30	12.0	0170 060 30											250			
	40	32			0170 060 40		0170 260 40							37.0	0153 060 040				
		24				0170 160 40		0170 360 40											
	45	37			0170 060 45		0170 260 45												
		32																	
	50	42			0170 060 50		0170 260 50								46.0		0153 060 050		
		32				0170 160 50		0170 360 50											
	55	45			0170 060 55														
	60	50			0170 060 60		0170 260 60								54.0		0153 060 060		
		37				0170 160 60		0170 360 60											
	70	60			0170 060 70		0170 260 70								64.0		0153 060 070		
		42				0170 160 70		0170 360 70											
	80	70			0170 060 80		0170 260 80								70.0		0153 060 080		
		50				0170 160 80		0170 360 80											
	90	50				0170 160 90		0170 360 90							50.0		0153 160 090		
	100	60				0170 160 100		0170 360 100							60.0		0153 160 100		
	110	70				0170 160 110		0170 360 110											
	120	70				0170 160 120		0170 360 120											
	130	70				0170 160 130		0170 360 130											
	140	70				0170 160 140		0170 360 140											
	150	70				0170 160 150		0170 360 150											
160	70		0170 160 160		0170 360 160														
180	70		0170 160 180		0170 360 180														
200	70		0170 160 200		0170 360 200														
220	70		0170 160 220		0170 360 220														
240	70		0170 160 240		0170 360 240														
260	70		0170 160 260		0170 360 260														
280	70		0170 160 280		0170 360 280														
300	70		0170 260 300		0170 360 300														

\* Single-flight thread

**ASSY® 3.0** dia. 4.0-4.5 mm  
**ASSY® 3.0** dia. 5.0-12.0 mm



With general construction permit



With general construction permit



ETA-11/0190