

SHEET-METAL BOLTS/NUTS



Art. No. 0964 129 08
600 parts

Hexagon-Head Sheet-Metal Screws, DIN 7976 with captive washer

Galvanized steel, blue passivated (A2K)

Art. No.		P. Qty.
0129 084 8...	4.8 x 16/19	100
0129 085 5...	5.5 x 13/16	100
0129 086 3...	6.3 x 16/20	50
0129 086 5...	6.3 x 16*	50
0129 088 0...	8.0 x 19	50

*With large washer dia.



Art. No. 0964 500 1
800 parts

Sheet-Metal Nuts

Galvanized steel, colorless passivated (A3A)

Art. No.		P. Qty.
0500 113 47	3.9	100
0500 113 62	4.2	100
0500 113 69	6.5	100
0500 114 03	6.5	100
0500 133 84	4.8	100
0500 121 9	3.5	100
0500 114 70	4.8	100
0500 115 77	5.5	100



Art. No. 0964 500 10
1,375 parts

Sheet-Metal and Spring Nuts

Galvanized steel, colorless passivated (A3A)

Art. No.		P. Qty.
0500 119 56	2.9	50
0500 121 9	3.5	50
0500 113 46	3.9	50
0500 113 62	4.2	50
0500 115 22	4.8	50
0500 115 77	5.5	50
0500 132 04	6.3	50
0500 114 27	6.3	50
0500 114 03	6.5	50
0500 113 69	6.5	100
0500 117 61	8.0	25
0500 111 84	2.5	200
0500 111 41	3.0	200
0500 111 83	3.5	200
0500 111 82	4.0	200

METRIC BOLTS



Art. No. 0964 057 1
665 parts

Hexagon Bolts, DIN 933, PC 8.8

Galvanized steel, blue passivated (A2K)

Art. No.		P. Qty.
0057 6 ...	M6 x 12/16/20	100
	M6 x 25	80
0057 8 ...	M8 x 16	60
	M8 x 20/25	50
	M8 x 30	40
0057 10 ...	M10 x 20/25	25
	M10 x 30	20
	M10 x 40	15



Art. No. 0964 096
430 parts

Hexagon Bolts, DIN 933

Stainless steel A2, non-rusting

Art. No.		P. Qty.
0096 6 ...	M6 x 10/16/20/25	50
	M6 x 30	25
0096 8 ...	M8 x 16/20/25	25
	M8 x 30/40	20
0096 10 ...	M10 x 20/25	20
	M10 x 30/35	15
	M10 x 40/50	10



Art. No. 0964 071
478 parts

Hexagon Inch Bolts and Nuts, UNF/SAE Grade 5

Galvanized steel, blue passivated (A2K)

Art. No.		P. Qty.
0331 ...	1/4"	125
	3/8"	50
	5/16"	60
0071 14 ...	1/4" x 1/2"; 3/4"; 1"; 1 1/4"; 1 1/2"	25
0071 516 ...	5/16" x 1/2"; 3/4"; 1"; 1 1/4"; 1 1/2"	10
	5/16" x 2"	8
0071 38 ...	3/8" x 1"	20
	3/8" x 1 1/4"; 1 1/2"	15
	3/8" x 1 3/4"	10