



FILLISTER-HEAD SCREWS

with slot
in accordance with DIN 84 (ISO 1207)

Nominal dia. d	Length l in mm	Bare brass Art. No.	P. Qty.	Bare steel 4.8 Art. No.	P. Qty.	Galv. steel 4.8, blue pass. Art. No.	P. Qty.	Galv. steel 4.8, yellow pass. Art. No.	P. Qty.	A2  Art. No.	P. Qty.	A4  Art. No.	P. Qty.	
M 2.5	25			0040 025 25	2000	0040 25 25	100/500	0040 725 25	500					
	28			0040 025 28		0040 25 28	2000							
	30			0040 025 30		0040 25 30			0040 725 30	2000				
	40					0040 25 40	100							
M 3	3			0040 03 3	2000	0040 3 3	2000	0040 73 3	2000	0287 3 3	1000		1000	
	4	0001 3 4	2000	0040 03 4		0040 3 4	100/500	0040 73 4		0287 3 4				
	5	0001 3 5	100/500	0040 03 5		0040 3 5		0040 73 5		0287 3 5				
	6	0001 3 6		0040 03 6		0040 3 6	100/1000	0040 73 6		0287 3 6				
	8	0001 3 8	250	0040 03 8		0040 3 8	500/1000	0040 73 8		0287 3 8				
	10	0001 3 10		0040 03 10		0040 3 10		0040 73 10		0287 3 10				
	12	0001 3 12		0040 03 12		0040 3 12		0040 73 12		0287 3 12				
	14	0001 3 14	2000	0040 03 14		0040 3 14	2000	0040 73 14		0287 3 14				
	16	0001 3 16	250	0040 03 16		0040 3 16	100/500	0040 73 16		0287 3 16				
	18	0001 3 18	2000	0040 03 18		0040 3 18		0040 73 18		0287 3 18				
	20	0001 3 20	250	0040 03 20		0040 3 20		0040 73 20		0287 3 20				
	22			0040 03 22		0040 3 22	2000	0040 73 22		0287 3 22				
	25	0001 3 25		0040 03 25		0040 3 25	100/250/1000	0040 73 25		0287 3 25				
	28			0040 03 28		0040 3 28	2000	0040 73 28						
	30	0001 3 30		0040 03 30		0040 3 30	100/500	0040 73 30		0287 3 30				
	32			0040 03 32		0040 3 32	1000							
	35	0001 3 35		0040 03 35		0040 3 35	100/250/1000	0040 73 35		0287 3 35				
	38		1000	0040 03 38		0040 3 38	2000							
	40	0001 3 40		0040 03 40		0040 3 40	100/250/1000	0040 73 40		0287 3 40				
	45	0001 3 45		0040 03 45		0040 3 45	100/300	0040 73 45		0287 3 45				
50	0001 3 50	250	0040 03 50	0040 3 50	100/250	0040 73 50	0287 3 50							
55			0040 03 55	0040 3 55	500	0040 73 55	0289 3 55							
60			0040 03 60	0040 3 60	100/250	0040 73 60	0289 3 60							
M 3.5	5			0040 035 5	2000	0040 35 5	2000	0040 735 5	2000		500			
	6			0040 035 6		0040 35 6		0040 735 6						
	8			0040 035 8		0040 35 8		0040 735 8						
	10			0040 035 10		0040 35 10		0040 735 10						
	12			0040 035 12		0040 35 12		0040 735 12						
	14			0040 035 14		0040 35 14								
	16			0040 035 16		0040 35 16		0040 735 16						
	18			0040 035 18		0040 35 18								
	20			0040 035 20		0040 35 20		0040 735 20						
	22			0040 035 22		0040 35 22		0040 735 22						
	25			0040 035 25		0040 35 25		0040 735 25						
	28			0040 035 28		0040 35 28								
	30			0040 035 30		0040 35 30		0040 735 30						
	32		1000	0040 035 32		0040 35 32								
	35			0040 035 35		0040 35 35								
	38			0040 035 38		0040 35 38								
40			0040 035 40	0040 35 40										
45			0040 035 45	0040 35 45										
50			0040 035 50	0040 35 50										
55			0040 035 55	0040 35 55	500									
60			0040 035 60	0040 35 60										
M 4	4			0040 04 4	2000	0040 4 4	100/500	0040 74 4	2000		200/500		1000	
	5	0001 4 5	500/2000	0040 04 5		0040 4 5	100/500/1000	0040 74 5		0287 4 5				
	6	0001 4 6	250	0040 04 6		0040 4 6	100/500	0040 74 6		0287 4 6				
	8	0001 4 8		0040 04 8		0040 4 8		0040 74 8		0287 4 8				
	10	0001 4 10		0040 04 10		0040 4 10	100/250/1000	0040 74 10		0287 4 10				
	12	0001 4 12		0040 04 12		0040 4 12	100/250	0040 74 12		0287 4 12				
	14	0001 4 14	2000	0040 04 14		0040 4 14	100	0040 74 14						
	16	0001 4 16	250	0040 04 16		0040 4 16	250/1000	0040 74 16		0287 4 16				
	18	0001 4 18	200	0040 04 18		0040 4 18	100/1000	0040 74 18		0287 4 18				
	20	0001 4 20	250	0040 04 20		0040 4 20	100/250/1000	0040 74 20		0287 4 20				
22			0040 04 22	0040 4 22	2000	0040 74 22	0287 4 22							
25	0001 4 25		0040 04 25	0040 4 25	100/250/1000	0040 74 25	0287 4 25							
28		250	0040 04 28	0040 4 28	2000	0040 74 28								
30	0001 4 30		0040 04 30	0040 4 30	100/250/1000	0040 74 30	0287 4 30							