

FILLISTER-HEAD SCREWS

with slot
in accordance with DIN 84 (ISO 1207)

Nominal dia. d	Length l in mm	Bare brass Art. No.	P. Qty.	Bare steel 4.8 Art. No.	P. Qty.	Galv. steel 4.8, blue pass. Art. No.	P. Qty.	Galv. steel 4.8, yellow pass. Art. No.	P. Qty.	A2 Art. No.	P. Qty.	A4 Art. No.	P. Qty.
M 4	32			0040 04 32	2000	0040 4 32	2000	0040 74 32				0289 4 32	
	35	0001 4 35		0040 04 35	1000	0040 4 35	1000/250/100	0040 74 35		0287 4 35	200/500	0289 4 35	
	38		100	0040 04 38	2000	0040 4 38	2000		1000			0289 4 38	
	40	0001 4 40		0040 04 40		0040 4 40	1000/250/100	0040 74 40		0287 4 40		0289 4 40	
	45	0001 4 45	500	0040 04 45		0040 4 45	250/100	0040 74 45		0287 4 45		0289 4 45	
	50	0001 4 50	100	0040 04 50		0040 4 50		0040 74 50		0287 4 50	500	0289 4 50	500
	55	0001 4 55	500	0040 04 55		0040 4 55	500	0040 74 55		0287 4 55		0289 4 55	
	60	0001 4 60		0040 04 60	500	0040 4 60	100	0040 74 60	500	0287 4 60		0289 4 60	
	65			0040 04 65		0040 4 65	500	0040 74 65					
	70			0040 04 70		0040 4 70	100	0040 74 70				0289 4 70	
	75			0040 04 75		0040 4 75	200	0040 74 75	200			0289 4 75	
	80	0001 4 80	200	0040 04 80		0040 4 80	100	0040 74 80	200			0289 4 80	
85			0040 04 85	200	0040 4 85	200					0289 4 85		
90			0040 04 90		0040 4 90						0289 4 90		
100			0040 04 100		0040 4 100	100	0040 74 100	100					
M 5	5			0040 05 5		0040 5 5	250	0040 75 5					
	6	0001 5 6		0040 05 6	2000	0040 5 6	100/250/1000	0040 75 6		0287 5 6	500	0289 5 6	
	8	0001 5 8	100	0040 05 8		0040 5 8	100/250	0040 75 8	2000	0287 5 8		0289 5 8	
	10	0001 5 10		0040 05 10		0040 5 10	100/250/1000	0040 75 10		0287 5 10		0289 5 10	
	12	0001 5 12		0040 05 12		0040 5 12	1000	0040 75 12	1000	0287 5 12	100/500	0289 5 12	500
	14	0001 5 14	1000	0040 05 14		0040 5 14	1000	0040 75 14	200/1000			0289 5 14	
	16	0001 5 16	100	0040 05 16		0040 5 16	100/250/1000	0040 75 16		0287 5 16		0289 5 16	
	18	0001 5 18	1000	0040 05 18		0040 5 18	100	0040 75 18		0287 5 18	500	0289 5 18	
	20	0001 5 20	100	0040 05 20	1000	0040 5 20	100/250/1000	0040 75 20	1000	0287 5 20	500/100	0289 5 20	
	22	0001 5 22	1000	0040 05 22		0040 5 22	1000	0040 75 22		0287 5 22	500		
	25	0001 5 25		0040 05 25		0040 5 25	100/1000	0040 75 25		0287 5 25		0289 5 25	
	28			0040 05 28		0040 5 28	1000	0040 75 28				0289 5 28	
	30	0001 5 30		0040 05 30		0040 5 30	50/100	0040 75 30		0287 5 30		0289 5 30	
	32		100	0040 05 32		0040 5 32	500				500/100		
	35	0001 5 35		0040 05 35		0040 5 35	100/1000	0040 75 35		0287 5 35		0289 5 35	
	38			0040 05 38		0040 5 38	500					0289 5 38	
	40	0001 5 40		0040 05 40	500	0040 5 40	50/100	0040 75 40	500	0287 5 40		0289 5 40	
	45	0001 5 45	500	0040 05 45		0040 5 45		0040 75 45		0287 5 45	100	0289 5 45	
	50	0001 5 50	100	0040 05 50		0040 5 50		0040 75 50		0287 5 50		0289 5 50	
	55	0001 5 55	500	0040 05 55		0040 5 55		0040 75 55		0287 5 55	500	0289 5 55	200
60	0001 5 60	100	0040 05 60		0040 5 60	100	0040 75 60		0287 5 60	100	0289 5 60		
65	0001 5 65		0040 05 65		0040 5 65		0040 75 65		0287 5 65		0289 5 65		
70	0001 5 70		0040 05 70		0040 5 70		0040 75 70		0287 5 70		0289 5 70		
75			0040 05 75		0040 5 75		0040 75 75				0289 5 75		
80	0001 5 80	200	0040 05 80	200	0040 5 80		0040 75 80	200	0287 5 80	200	0289 5 80		
85			0040 05 85		0040 5 85		0040 75 85				0289 5 85		
90	0001 5 90	100	0040 05 90		0040 5 90	200	0040 75 90		0287 5 90		0289 5 90		
100	0001 5 100	200	0040 05 100		0040 5 100	100	0040 75 100		0287 5 100	100	0289 5 100		
M 6	6	0001 6 6	1000	0040 06 6		0040 6 6	100/500	0040 76 6					
	8	0001 6 8	1000/500	0040 06 8		0040 6 8	100/500	0040 76 8		0287 6 8	200	0289 6 8	
	10	0001 6 10	100	0040 06 10		0040 6 10	250/100/1000	0040 76 10		0287 6 10		0289 6 10	
	12	0001 6 12		0040 06 12	1000	0040 6 12		0040 76 12	1000	0287 6 12		0289 6 12	
	14	0001 6 14	1000	0040 06 14		0040 6 14	1000	0040 76 14				0289 6 14	
	16	0001 6 16	100	0040 06 16		0040 6 16	250/100/1000	0040 76 16		0287 6 16	100	0289 6 16	
	18	0001 6 18	1000	0040 06 18		0040 6 18	1000	0040 76 18				0289 6 18	
	20	0001 6 20	100	0040 06 20		0040 6 20	250/100/1000	0040 76 20		0287 6 20		0289 6 20	200
	22	0001 6 22	500	0040 06 22		0040 6 22	500	0040 76 22		0287 6 22	200	0289 6 22	
	25	0001 6 25		0040 06 25		0040 6 25	50/250	0040 76 25		0287 6 25		0289 6 25	
	28			0040 06 28		0040 6 28	500	0040 76 28				0289 6 28	
	30	0001 6 30		0040 06 30		0040 6 30	50/250	0040 76 30		0287 6 30		0289 6 30	
	32		100	0040 06 32	500	0040 6 32	500		500			0289 6 32	
	35	0001 6 35		0040 06 35		0040 6 35	100	0040 76 35		0287 6 35		0289 6 35	
38			0040 06 38		0040 6 38	500					0289 6 38		
40	0001 6 40		0040 06 40		0040 6 40		0040 76 40		0287 6 40		0289 6 40		
45	0001 6 45	200	0040 06 45		0040 6 45	100	0040 76 45		0287 6 45	200	0289 6 45		
50	0001 6 50	100	0040 06 50	200	0040 6 50	200	0040 76 50	200	0287 6 50	100	0289 6 50	100	