

ASSEMBLY CLEANER 1A



Highly active & safe assembly and parts cleaner.

Increased safety without loss of performance

- TÜV-tested explosion and fire behavior as per test method no. PPP 53285:2006.

Good cleaning performance

- Brake dust, grease and other dirt are removed quickly and reliably.
- Product flashes off quickly with no residue.

Significantly reduces the risk potential in the workplace

- Significantly reduced explosion risk in comparison with conventional products.
- Minimized fire risk.
- Spray can contains non-flammable propellant.
- AOX- and aromatic compound-free.

Designation/Container	Contents	Art. no.	PU/qty.
Spray can	500 ml	0890 106 500	24
Canister	20 l	0890 106 520	
Barrel	60 l	0890 106 560	
Pump spray bottle, unfilled	1 l	0891 503 006	
REFILLO®mat can	400 ml	0891 881 26	1
REFILLO®mat	-	0961 891 022	
ORSY® component for 60 l barrel	-	0961 891 002	
Grounding cable for ORSY®protec	-	0891 870 76	
ORSY®protec	-	0891 870 77	6

Areas of application:

Specially developed part cleaner for the reliable cleaning of brake dust, grease, soot and other soiling.

For use on disc and drum brakes, engine assemblies, tools of all types, assemblies, clutch parts and for other maintenance, repair and mounting work.

How to use:

Do not spray on hot parts. Check the

compatibility of plastic & rubber parts and painted surfaces in a non-visible area before applying.



Using this QR code, you can learn more on the topic of "Using assembly and part cleaner in automotive and metal workshops."

This information is only a recommendation based on our experience. Test in an inconspicuous area when using on metal surfaces. Preliminary testing required! For further information, see the technical information leaflet.

Silicone-free



Art no. 0891 870 76



Art no. 0891 870 77

Accessories:

Tap for 20 l canister, art. no. 0891 302 03

60 l barrel, art. no. 0891 302 07