


Nominal dia. d in mm	Length l in mm	Galvanized steel, blue pass. Art. No.	P. Qty.	A2  Art. No.	P. Qty.
5.5	13	0114 55 13	100	0122 55 13	500
	16	0114 55 16		0122 55 16	
	19	0114 55 19		0122 55 19	
	22	0114 55 22		0122 55 22	
	25	0114 55 25		0122 55 25	
	32	0114 55 32		0122 55 32	
	38			0122 55 38	100
	45			0122 55 45	100
	50			0122 55 50	500
	60			0122 55 60	100
	70			0122 55 70	
	80			0122 55 80	
	90			0122 55 90	
	100			0122 55 100	
110	0122 55 110				
6.3	9.5			0114 63 95	1000
	13	0114 63 13	100	0122 63 13	500
	16	0114 63 16		0122 63 16	
	19	0114 63 19		0122 63 19	
	22	0114 63 22		0122 63 22	
	25	0114 63 25		0122 63 25	
	32	0114 63 32		0122 63 32	
	38	0114 63 38		0122 63 38	500
	45	0114 63 45		0122 63 45	200
	50	0114 63 50		0122 63 50	100
	55			0122 63 55	200
	60	0114 63 60		0122 63 60	
	70	0114 63 70	250	0122 63 70	
	80			0122 63 80	
90	0114 63 90	100	0122 63 90	100	
100			0122 63 100		
110			0122 63 110		
8.0	16	0114 8 16	100	0122 8 16	200
	19	0114 8 19		0122 8 19	
	22	0114 8 22		0122 8 22	
	25	0114 8 25		0122 8 25	
	32	0114 8 32	250	0122 8 32	100
	38	0114 8 38	100	0122 8 38	
	45			0122 8 45	
	50	0114 8 50	500	0122 8 50	
	60			0122 8 60	
70	0114 8 70	0122 8 70			
80	0114 8 80	250			