



Workshop Cart

for LPG conversion

- Mobile LPG gas conversion workplace → Great flexibility.
- Fast access to common tools and processing materials thanks to optimum overview
→ Reduction of expensive searching times.
- Individual expansion options thanks to broad range of accessories (hooks and holders available as an option).

Art. No. 0962 606 002

P. Qty. 1

Contents

Designation	Art. No.	P. Qty.
Hand-Held LED Lamp	0827 940 030	1
Sound-Insulation Boards, self-adhesive	0890 100 060	
Brake Cleaner	0890 108 7	
Body Cavity Sealant	0893 081	3
Probe for Body Cavity Sealant	0891 081	
Rust Stop Primer	0890 191	
Leak Detection Spray	0890 27	1
Interior Cleaner	0893 033	
Pipe Sealant	0893 577 050	
Silicone Spray Grease	0893 223	
Underseal (wax)	0892 078	
Screw Lock	0893 243 025	

Designation	Art. No.	P. Qty.
Glues and Seals Combination, white	0893 236 110	1
Wiring Harness Wrapping Hose	0771 00 90	25
Marten Protection Tube, ND 8.8 mm	0771 990 08	50
Marten Protection Tube, ND 10 mm	0771 990 10	10
Marten Protection Tube, ND 17 mm	0771 990 17	
Edge Protection Profile	0961 002 5	
Rivet Nut Pliers (M5/M6/M8)	0948 800	1
Rubber Mallet	0715 734 08	
Body Hammer	0715 74 20	
Hammer, 300 g	0715 731 30	
Armored Adhesive Tape	0992 381 50	
4-Wire Cable (1.5 mm ²)	0893 243 025	

Designation	Art. No.	P. Qty.	Drawer No.
Drill Bit, 20 cm	0625 200 030	1	1
Spot-Weld Remover	0710 006 6		
Drill Bit, 5 mm long	0627 005 245		
Bottoming Tap, M6	0653 091 01	var.	1
Mounting for Rivet Nut Pliers	0948 800		
Stepped Drill Bit	0694 123 630	1	2
Deburring Unit	0714 91 20		
Hole Saw, 52 mm	0632 52		
Hole Saw, 54 mm	0632 54		
Pipe Cutter	0714 551 116		
Mounting for Hole Saw	0632 02		
Pipe Bending Pliers	0714 05 011		
Sheet Metal Shears, left-handed	0714 03 01		
Sheet Metal Shears, right-handed	0714 03 02		
Axle Bellows Pliers	0714 546 23		
Hose Clamp Pliers, rigid	0714 577 111	1	3
Hose Clamp Pliers, flexible	0714 577 112		
Water Pump Pliers	0714 01 63		
Wire Stripping Pliers	0714 01 50		
Side Cutters, electronic	0714 01 51		
Long-Nose Pliers, long	0714 01 57		
Long-Nose Pliers, short	0714 01 59		
Hose Clamp, small (metal)	0989 911 922		
Hose Shears	0855 20 02		
Set of Pinch-Off Pliers for Refrigerators	0714 601 931		
Phillips Screwdriver, long	0613 262 2	100	4
Torx (20) Screwdriver, 25 mm	0613 464 20		
Slotted Screwdriver, long	0613 261 04		
Bit Holder, long	0614 176 729		
Mini Drill Chuck	0713 92 04		
Magnet, flexible	0715 35 35		
Screw Tap Die, long	0715 42 04		
Hose Clam Screwdriver, 6 mm	0613 286 06		
Hose Clam Screwdriver, 7 mm	0613 286 07		
Hand Deburrer	0713 421 510		
Carpet Knife	0715 66 35	25	
Bit Assortment	0614 250 7		
Bit Assortment	0614 250 2		
Cable Connector Ring Lug	0558 521 9		
Blade Fuse, 15 amps	0731 015		
Insulating Tape	0985 101		
Cable Tie, Plastic Lug	0502 161		
Cable Tie, Plastic Lug	0502 141		
Cable Tie, Plastic Lug	0502 121		
Blind Rivet 5x12	0938 5 12		
Rivets Rivet Nut Pliers M5 (6k)	0948 305 12	100	
Rivets Rivet Nut Pliers M6 (6k)	0948 306 14		
Cable Bushing	0561 665 0	25	
Cable Bushing	0561 664 6		

Designation	Art. No.	P. Qty.	Drawer No.
One-Ear Clamp	0541 007 210	10	4
One-Ear Clamp	0541 007 157		
Hose Clamp	0539 112 22	50	5
Hose Clamp	0539 116 27		
Pipe Clamp (rubberized)	0542 8 12	50	6
Pipe Clamp (rubberized)	0542 8 15		
Pipe Clamp (rubberized)	0542 10 12		
Pipe Clamp, rubberized, 20 mm	0542 20 15	200	7
Pipe Clamp, rubberized, 25 mm	0542 25 15		
Hexagon Bolt, full, M10	0057 10 20	100	8
Self-Tapping Screws	0206 48 16		
Stop Nut, M12	0368 012		
Nuts, M10	0317 10		
Stop Nuts, M6	0368 06		
Nut, M6	0317 6		
Nut, M5	0317 5		
Spring Washer	0435 5		
Washer, M10	0411 10 303		
Washer, M12	0411 12 40		
Fender Washer, M6	0416 6	300	
Front glass	0407 6		
Assortment of Thread Tap	0964 961 7	1	
Gas Soldering Iron	0984 990 100		
Butane Gas	0893 250 001	5	
Heat-Shrink Hose, ID 6.4 mm	0771 806 4		
Heat-Shrink Hose, ID 9.5 mm	0771 809 5		
Heat-Shrink Hose, ID 19.0 mm	0771 819 0	1	
Gas Leak Detector	0715 53 250		
Battery-Powered Screwdriver, small	0700 662 2		

