

SET SCREWS

DIN EN ISO 4027

Nominal dia.	Length l in mm	Bare steel Art. No.	P. Qty.	Galvanized steel Blue-passivated Art. No.	P. Qty.
M16	45	0256 16 45	10	0256 016 45	10
	50	0256 16 50		0256 016 50	
	60	0256 16 60		0256 016 60	
	70	0256 16 70		0256 016 70	
	80	0256 16 80		0256 016 80	
	100	0256 16 100			
	120	0256 16 120			

Can be stored in ORSY®

replaces DIN 914

with Allen socket and flattened tip

Bare steel, 45 H
Galvanized steel, blue passivated (A2K), 45 H

Hardness 45H corresponds to a hardness of 450 HV.

The standard version of the tip is 90°, but very short lengths (those marked with an *) have an angle of 120°.

DIN 914 has been retracted and replaced by international standard DIN EN ISO 4027.