

WATER HOSE PROFESSIONAL



Multi-layer high-quality PVC water hose with high-strength polyester textile lining.

Highly flexible

Kink-proof and abrasion-resistant

Cannot be twisted

Does not twist or get tangled up

Cold- and heat-resistant

Silicone-free

UV-resistant

No algal growth

Cadmium- and barium-free

Very smooth interior lining

Optimum water flow

Art. No.	0886 001 200	0886 001 201	0886 001 210	0886 001 211	0886 001 220
P. Qty.	50	30	50	25	50
Material	Polyvinyl chloride - PVC	Polyvinyl chloride - PVC	Polyvinyl chloride - PVC	Polyvinyl chloride - PVC	Polyvinyl chloride - PVC
Colour	Yellow	Yellow	Yellow	Yellow	Yellow
Material of the mesh	Polyester	Polyester	Polyester	Polyester	Polyester
Internal diameter in inches	1/2 in	1/2 in	3/4 in	3/4 in	1 in
Internal diameter	12.5 mm	12.5 mm	18.8 mm	18.8 mm	25 mm
Wall thickness	2.55 mm	2.55 mm	3.3 mm	3.3 mm	3.65 mm
Hose length	50 m	30 m	50 m	25 m	50 m
Working pressure	10 bar	10 bar	9 bar	9 bar	8 bar
Conditions for operating pressure	at 23 °C	at 23 °C	at 23 °C	at 23 °C	at 23 °C
Burst pressure	25 bar	25 bar	23 bar	23 bar	20 bar
Burst pressure conditions	at 23 °C	at 23 °C	at 23 °C	at 23 °C	at 23 °C
Min./max. temperature resistance	-15 bis 60 °C	-15 bis 60 °C	-15 bis 60 °C	-15 bis 60 °C	-15 bis 60 °C
Bending radius	67.5 mm	67.5 mm	95 mm	95 mm	125 mm