

PNEUMATIC IMPACT SCREWDRIVER DSS 1/2" COMPACT



Very powerful yet compact pneumatic impact screwdriver with outstanding power-to-weight ratio. Maximum recommended screw size: M16.

Long service life and optimal balance distribution

Rugged, well-balanced unit in aluminium housing.

Very handy and user-friendly

- Rubberised handle prevents unpleasant cooling
- User-friendly clockwise/anti-clockwise changeover and adjustable button

Compact and extremely powerful jumbo hammer mechanism

High power development with small size and low weight, up to 1,100 Nm break-away torque.

Optimum and user-friendly adjustment to any application, at any time

Three-stage power setting for clockwise rotation, with sensitive trigger

2 Years WÜRTH MASTERPLUS Warranty for wear damage

The current WÜRTH MASTERPLUS warranty conditions must be observed.

3 Years Warranty on manufacturing and material defects

Excluded are damages caused by improper use, overloading or failure to observe the operating instructions.

Art. No.	5714 302 0
P. Qty.	1
Tool holding device	1/2-inch external square
Max. working torque	678 Nm
Max. releasing torque	1100 Nm
Sound-pressure level	102 dB
Vibration	7.5 m/s ²
Weight of machine	1.34 kg

Related products	Art. No.
Plug-in nipple S2000 MT	0699 100 614

Application area

Ideal where space is limited, e.g. gearbox, engine compartment, brakes

Notice

- Impact screwdrivers are not torque screwdrivers. Connections requiring a specific torque must be checked by means of a torque measuring device after tightening with the impact screwdriver.
- When the impact screwdriver is used regularly, a little oil should be added daily through the compressed air supply.
- Plug-in nipple not included in the scope of delivery