



























































































## TWIST DRILL BIT HSCO DIN 338 TYPE RN OXIDE

| Color Coding System  |   |                        | Diameter (Ø) | Length | Chip flute length | Art. No.            | P. Qty. |
|--|---|------------------------|--------------|--------|-------------------|---------------------|---------|
|    |    | Stainless steel; Steel | 8.7 mm       | 125 mm | 81 mm             | <b>0626 000 870</b> | 1       |
|    |    | Stainless steel; Steel | 8.8 mm       | 125 mm | 81 mm             | <b>0626 000 880</b> | 1       |
|    |    | Stainless steel; Steel | 8.9 mm       | 125 mm | 81 mm             | <b>0626 000 890</b> | 1       |
|    |    | Stainless steel; Steel | 9 mm         | 125 mm | 81 mm             | <b>0626 000 900</b> | 1       |
|    |    | Stainless steel; Steel | 9.1 mm       | 125 mm | 81 mm             | <b>0626 000 910</b> | 1       |
|    |    | Stainless steel; Steel | 9.2 mm       | 125 mm | 81 mm             | <b>0626 000 920</b> | 1       |
|    |    | Stainless steel; Steel | 9.3 mm       | 125 mm | 81 mm             | <b>0626 000 930</b> | 1       |
|    |    | Stainless steel; Steel | 9.4 mm       | 125 mm | 81 mm             | <b>0626 000 940</b> | 1       |
|    |    | Stainless steel; Steel | 9.5 mm       | 125 mm | 81 mm             | <b>0626 000 950</b> | 1       |
|    |    | Stainless steel; Steel | 9.6 mm       | 133 mm | 87 mm             | <b>0626 000 960</b> | 1       |
|    |    | Stainless steel; Steel | 9.7 mm       | 133 mm | 87 mm             | <b>0626 000 970</b> | 1       |
|    |    | Stainless steel; Steel | 9.8 mm       | 133 mm | 87 mm             | <b>0626 000 980</b> | 1       |
|    |    | Stainless steel; Steel | 9.9 mm       | 133 mm | 87 mm             | <b>0626 000 990</b> | 1       |
|    |    | Stainless steel; Steel | 10 mm        | 133 mm | 87 mm             | <b>0626 001 000</b> | 1       |
|   |   | Stainless steel; Steel | 10.1 mm      | 133 mm | 87 mm             | <b>0626 001 010</b> | 1       |
|  |  | Stainless steel; Steel | 10.2 mm      | 133 mm | 87 mm             | <b>0626 001 020</b> | 1       |
|  |  | Stainless steel; Steel | 10.3 mm      | 133 mm | 87 mm             | <b>0626 001 030</b> | 1       |
|  |  | Stainless steel; Steel | 10.4 mm      | 133 mm | 87 mm             | <b>0626 001 040</b> | 1       |
|  |  | Stainless steel; Steel | 10.5 mm      | 133 mm | 87 mm             | <b>0626 001 050</b> | 1       |
|  |  | Stainless steel; Steel | 10.6 mm      | 133 mm | 87 mm             | <b>0626 001 060</b> | 1       |
|  |  | Stainless steel; Steel | 10.7 mm      | 142 mm | 94 mm             | <b>0626 001 070</b> | 1       |
|  |  | Stainless steel; Steel | 10.8 mm      | 142 mm | 94 mm             | <b>0626 001 080</b> | 1       |
|  |  | Stainless steel; Steel | 10.9 mm      | 142 mm | 94 mm             | <b>0626 001 090</b> | 1       |
|  |  | Stainless steel; Steel | 11 mm        | 142 mm | 94 mm             | <b>0626 001 100</b> | 1       |
|  |  | Stainless steel; Steel | 11.1 mm      | 142 mm | 94 mm             | <b>0626 001 110</b> | 1       |
|  |  | Stainless steel; Steel | 11.2 mm      | 142 mm | 94 mm             | <b>0626 001 120</b> | 1       |
|  |  | Stainless steel; Steel | 11.3 mm      | 142 mm | 94 mm             | <b>0626 001 130</b> | 1       |
|  |  | Stainless steel; Steel | 11.4 mm      | 142 mm | 94 mm             | <b>0626 001 140</b> | 1       |
|  |  | Stainless steel; Steel | 11.5 mm      | 142 mm | 94 mm             | <b>0626 001 150</b> | 1       |
|  |  | Stainless steel; Steel | 11.6 mm      | 142 mm | 94 mm             | <b>0626 001 160</b> | 1       |
|  |  | Stainless steel; Steel | 11.7 mm      | 142 mm | 94 mm             | <b>0626 001 170</b> | 1       |
|  |  | Stainless steel; Steel | 11.8 mm      | 142 mm | 94 mm             | <b>0626 001 180</b> | 1       |
|  |  | Stainless steel; Steel | 11.9 mm      | 151 mm | 101 mm            | <b>0626 001 190</b> | 1       |
|  |  | Stainless steel; Steel | 12 mm        | 151 mm | 101 mm            | <b>0626 001 200</b> | 1       |
|  |  | Stainless steel; Steel | 12.1 mm      | 151 mm | 101 mm            | <b>0626 001 210</b> | 1       |
|  |  | Stainless steel; Steel | 12.2 mm      | 151 mm | 101 mm            | <b>0626 001 220</b> | 1       |
|  |  | Stainless steel; Steel | 12.3 mm      | 151 mm | 101 mm            | <b>0626 001 230</b> | 1       |
|  |  | Stainless steel; Steel | 12.4 mm      | 151 mm | 101 mm            | <b>0626 001 240</b> | 1       |
|  |  | Stainless steel; Steel | 12.5 mm      | 151 mm | 101 mm            | <b>0626 001 250</b> | 1       |
|  |  | Stainless steel; Steel | 12.6 mm      | 151 mm | 101 mm            | <b>0626 001 260</b> | 1       |
|  |  | Stainless steel; Steel | 12.7 mm      | 151 mm | 101 mm            | <b>0626 001 270</b> | 1       |
|  |  | Stainless steel; Steel | 12.8 mm      | 151 mm | 101 mm            | <b>0626 001 280</b> | 1       |
|  |  | Stainless steel; Steel | 12.9 mm      | 151 mm | 101 mm            | <b>0626 001 290</b> | 1       |
|  |  | Stainless steel; Steel | 13 mm        | 151 mm | 101 mm            | <b>0626 001 300</b> | 1       |
|  |  | Stainless steel; Steel | 13.1 mm      | 151 mm | 101 mm            | <b>0626 001 310</b> | 1       |
|  |  | Stainless steel; Steel | 13.5 mm      | 160 mm | 108 mm            | <b>0626 001 350</b> | 1       |
|  |  | Stainless steel; Steel | 14 mm        | 160 mm | 108 mm            | <b>0626 001 400</b> | 1       |