














## TWIST DRILL BIT HSCO DIN 338 TYPE RN OXIDE

Color Coding System	Diameter (Ø)	Length	Chip flute length	Art. No.	P. Qty.
 Stainless steel; Steel	14.2 mm	169 mm	114 mm	<b>0626 001 420</b>	1
 Stainless steel; Steel	14.5 mm	169 mm	114 mm	<b>0626 001 450</b>	1
 Stainless steel; Steel	15 mm	169 mm	114 mm	<b>0626 001 500</b>	1
 Stainless steel; Steel	15.5 mm	178 mm	120 mm	<b>0626 001 550</b>	1
 Stainless steel; Steel	16 mm	178 mm	120 mm	<b>0626 001 600</b>	1
 Stainless steel; Steel	16.5 mm	184 mm	125 mm	<b>0626 001 650</b>	1
 Stainless steel; Steel	17 mm	184 mm	125 mm	<b>0626 001 700</b>	1
 Stainless steel; Steel	17.5 mm	191 mm	130 mm	<b>0626 001 750</b>	1
 Stainless steel; Steel	18 mm	191 mm	130 mm	<b>0626 001 800</b>	1
 Stainless steel; Steel	18.5 mm	198 mm	135 mm	<b>0626 001 850</b>	1
 Stainless steel; Steel	19 mm	198 mm	135 mm	<b>0626 001 900</b>	1
 Stainless steel; Steel	19.5 mm	205 mm	140 mm	<b>0626 001 950</b>	1
 Stainless steel; Steel	20 mm	205 mm	140 mm	<b>0626 002 000</b>	1