

AUTOMATIC SELF-ADJUSTING WIRE STRIPPING PLIERS



Recessed cable cutter for Cu and Al conductors.
Stranded conductors up to 10.0 mm² and single wire up to 6.0 mm²

Replaceable blades block and length stop

Easily adjustable length stop



Art. No.	0714 109 010
P. Qty.	1
Min./max. wire cross section	0.03-10 mm ²
Min./max. American Wire Gauge (AWG) (AWG)	32-7
Length (L)	195 mm
Material	Plastic/steel
Material of the grip handle	2-component plastic

Fully automatic adaptation to single, multi and fine-wire conductors. No manual fine adjustment necessary.

Robust and durable

Improved blade geometry, metallic clamping jaws

Ergonomically designed 2-component handle

For comfortable, effortless work

Particularly smooth-running mechanism and low weight

Made in Germany

Notice

Not suitable for highly flexible and reinforced insulation materials or for multi-layer insulation.

REPLACEMENT BLADES BLOCK



For automatic self-adjusting wire stripping pliers

Notice

Not suitable for highly flexible and reinforced insulation materials or for multi-layer insulation.

Art. No.	0714 109 110
P. Qty.	1
Min./max. wire cross section	0.03-10 mm ²
Colour	Black