

## FLAT WASHER FOR HEXAGON BOLTS AND NUTS

DIN 125 galvanised steel, blue passivated (A2K)

Suitable for screw thread	Internal diameter (d <sub>1</sub> )	Outer diameter (d <sub>2</sub> )	Thickness (h <sub>1</sub> )	Form	Art. No.	P. Qty.
M36	37 mm	66 mm	5 mm	A	<b>0407 993 6</b>	50
M36	37 mm	66 mm	5 mm	B	<b>0407 36</b>	50
M38	39 mm	72 mm	6 mm	B	<b>0407 38</b>	50
M39	40 mm	72 mm	6 mm	A	<b>0407 993 9</b>	25
M39	40 mm	72 mm	6 mm	B	<b>0407 39</b>	20/25
M40	41 mm	72 mm	6 mm	A	<b>0407 994 0</b>	50
M40	41 mm	72 mm	6 mm	B	<b>0407 40</b>	10/50
M42	43 mm	78 mm	7 mm	A	<b>0407 994 2</b>	25
M42	43 mm	78 mm	7 mm	B	<b>0407 42</b>	20/25
M45	46 mm	85 mm	7 mm	A	<b>0407 994 5</b>	25
M45	46 mm	85 mm	7 mm	B	<b>0407 45</b>	25
M48	50 mm	92 mm	8 mm	B	<b>0407 48</b>	20
M50	52 mm	92 mm	8 mm	B	<b>0407 50</b>	20
M52	54 mm	98 mm	8 mm	A	<b>0407 995 2</b>	25
M52	54 mm	98 mm	8 mm	B	<b>0407 52</b>	20
M56	58 mm	105 mm	9 mm	B	<b>0407 56</b>	10
M60	62 mm	110 mm	9 mm	A	<b>0407 996 0</b>	1
M60	62 mm	110 mm	9 mm	B	<b>0407 60</b>	10
M64	66 mm	115 mm	9 mm	A	<b>0407 996 4</b>	1
M64	66 mm	115 mm	9 mm	B	<b>0407 64</b>	10
M72	74 mm	125 mm	10 mm	B	<b>0407 72</b>	5
M76	78 mm	135 mm	10 mm	B	<b>0407 76</b>	5
M80	82 mm	140 mm	12 mm	B	<b>0407 82</b>	5
M90	93 mm	160 mm	12 mm	A	<b>0407 999 0</b>	1
M90	93 mm	160 mm	12 mm	B	<b>0407 90</b>	1
M110	114 mm	185 mm	14 mm	B	<b>0407 991 10</b>	10

