

STRUCTURAL ADHESIVE BOND+SEAL

Chemical basis	Single component polyurethane
Min. skin-formation time	45 min
Min./max. skin-formation time	45-60 min
Full curing speed/conditions	3 mm/d / 23 °C and 50% relative humidity, moisture curing
Min./max. processing temperature	5 to 35 °C
Min./max. temperature resistance	-40 to 90 °C
Shelf life from production	12 Month
Max. short-term temperature resistance	120 °C

Contents	Colour	Art. No.	P. Qty.
300 ml	White	0890 100 1	1 / 12 / 24
300 ml	Grey	0890 100 2	1 / 12 / 24
300 ml	Black	0890 100 3	1 / 12 / 24
300 ml	Dark brown	0890 100 4	1 / 12
300 ml	Light brown	0890 100 5	1 / 12
300 ml	Sand beige	0890 100 6	1 / 12
70 ml	White	0890 100 11	1 / 24
70 ml	Black	0890 100 31	1 / 24
400 ml	White	0890 100 111	12
400 ml	Grey	0890 100 112	12
400 ml	Black	0890 100 113	12
600 ml	White	0890 100 181	20
600 ml	Grey	0890 100 182	20
600 ml	Black	0890 100 183	20
600 ml	Dark brown	0890 100 184	20

Related products	Art. No.
Standard application nozzle	0890 100 099
Surface cleaner Activating Cleaner	0890 100 60
Surface bonding agent Primer for Metal	0890 100 61
Surface bonding agent Adhesion Plus for plastic/wood/stone	0890 100 62
Adhesive remover	0890 100 63
Application gun WIT	0891 003
Special cartridge nozzle V-Cut	0891 651 13