

# STECKVERBINDUNGEN STANDARDAUSFÜHRUNG

**Gerade Steckverschraubung  
mit Außensechskant**



ø dmm	R	Art.-Nr.	Sonderbestellung-Nr.	VE/St.
2	M3	0699 110 302	-	10
3,2	M3	0699 110 323	-	
	M5	0699 110 523	834223/KQ2H23-M5N	
	R1/8	0699 111 123	834223/KQ2H23-01NS	
	R1/4	0699 111 223	834223/KQ2H23-02NS	
4	M3	0699 110 304	-	
	M5	0699 110 504	834223/KQ2H04-M5N	
	R1/8	0699 111 104	834223/KQ2H04-01NS	
	R1/4	0699 111 204	834223/KQ2H04-02NS	
6	M5	0699 110 506	834223/KQ2H06-M5N	
	R1/8	0699 111 106	834223/KQ2H06-01NS	
	R1/4	0699 111 206	834223/KQ2H06-02NS	
	R3/8	0699 111 306	834223/KQ2H06-03NS	
8	R1/8	0699 111 108	834223/KQ2H08-01NS	
	R1/4	0699 111 208	834223/KQ2H08-02NS	
	R3/8	0699 111 308	834223/KQ2H08-03NS	
10	R1/8	0699 111 110	834223/KQ2H10-01NS	5
	R1/4	0699 111 021	834223/KQ2H10-02NS	
	R3/8	0699 111 310	834223/KQ2H10-03NS	
	R1/2	0699 111 041	834223/KQ2H10-04NS	
12	R1/4	0699 111 212	834223/KQ2H12-02NS	
	R3/8	0699 111 312	834223/KQ2H12-03NS	
	R1/2	0699 111 412	834223/KQ2H12-04NS	
16	R1/4	0699 111 216	834223/KQ2H16-02NS	
	R3/8	0699 111 316	834223/KQ2H16-03NS	
	R1/2	0699 111 416	834223/KQ2H16-04NS	
<b>Ausführung</b>	Messing	Messing/Nickel		

**Einschraubwinkel  
360° schwenkbar**



ø dmm	R	Art.-Nr.	Sonderbestellung-Nr.	VE/St.
2	M3	0699 114 302	-	10
3,2	M3	0699 114 323	-	
	M5	0699 114 523	834223/KQ2L23-M5N	
	R1/8	0699 116 123	834223/KQ2L23-01NS	
4	M3	0699 114 304	-	
	M5	0699 114 504	834223/KQ2L04-M5N	
	M6	0699 114 604	834223/KQ2L04-M6N	
	R1/8	0699 116 104	-	
6	R1/4	0699 116 204	834223/KQ2L04-02NS	
	M5	0699 114 506	-	
	M6	0699 114 606	834223/KQ2L06-M6N	
	R1/8	0699 116 106	-	
8	R1/4	0699 116 206	834223/KQ2L06-02NS	
	R3/8	0699 116 306	834223/KQ2L06-03NS	
	R1/8	0699 116 108	834223/KQ2L08-01NS	
	R1/4	0699 116 208	834223/KQ2L08-02NS	
10	R3/8	0699 116 308	834223/KQ2L08-03NS	5
	R1/8	0699 116 110	834223/KQ2L10-01NS	
	R1/4	0699 116 210	834223/KQ2L10-02NS	
	R3/8	0699 116 310	834223/KQ2L10-03NS	
12	R1/2	0699 116 410	834223/KQ2L10-04NS	
	R1/4	0699 116 212	834223/KQ2L12-02NS	
	R3/8	0699 116 312	834223/KQ2L12-03NS	
	R1/2	0699 116 412	834223/KQ2L12-04NS	
16	R1/4	0699 116 216	834223/KQ2L16-02NS	
	R3/8	0699 116 316	834223/KQ2L16-03NS	
	R1/2	0699 116 416	834223/KQ2L16-04NS	
<b>Ausführung</b>	Messing	Messing/Nickel		

**Einschraubwinkel 45°  
360° schwenkbar**



ø dmm	R	Art.-Nr.	Sonderbestellung-Nr.	VE/St.
4	M5	0699 113 504	834223/KQ2K04-M5N	10
	M6	0699 113 604	834223/KQ2K04-M6N	
	R1/8	0699 112 104	834223/KQ2K04-01NS	
	R1/4	0699 112 204	834223/KQ2K04-02NS	
6	M5	0699 113 506	834223/KQ2K06-M5N	
	M6	0699 113 606	834223/KQ2K06-M6N	
	R1/8	0699 112 106	834223/KQ2K06-01NS	
	R1/4	0699 112 206	834223/KQ2K06-02NS	
6	R3/8	0699 112 306	834223/KQ2K06-03NS	
	<b>Ausführung</b>	Messing	Messing/Nickel	

ø dmm	R	Art.-Nr.	Sonderbestellung-Nr.	VE/St.
8	R1/8	0699 112 108	834223/KQ2K08-01NS	10
	R1/4	0699 112 208	834223/KQ2K08-02NS	
	R3/8	0699 112 308	834223/KQ2K08-03NS	
10	R1/8	0699 112 110	834223/KQ2K10-01NS	5
	R1/4	0699 112 210	834223/KQ2K10-02NS	
12	R3/8	0699 112 310	834223/KQ2K10-03NS	
	R1/4	0699 112 212	834223/KQ2K12-02NS	
	R3/8	0699 112 312	834223/KQ2K12-03NS	
12	R1/2	0699 112 412	834223/KQ2K12-04NS	
	16	R1/2	0699 112 416	
<b>Ausführung</b>	Messing	Messing/Nickel		