

STECKVERBINDUNGEN STANDARDAUSFÜHRUNG

- Steckanschluss: \varnothing ext. 2; 3,2; 4; 6; 8; 10; 12; 16 mm
- Gewinde: M3; M5; M6; R(Rc) 1/8; 1/4; 3/8; 1/2
- Schnelle und einfache Montage/Demontage
- Kompakt und leicht

T-Steckverbindung 360°schwenkbar



Y-Steckverschraubung 4-fach



\varnothing d mm	R	Art.-Nr.	Sonderbestellung-Nr.	VE/St.
2	M3	0699 132 302	-	10
3,2		0699 132 323	-	
		0699 132 304	-	
4	M5	0699 132 504	834223/KQ2T04-M5N	
	R1/8	0699 133 104	834223/KQ2T04-01NS	
	R1/4	0699 133 204	834223/KQ2T04-02NS	
6	M5	0699 132 506	834223/KQ2T06-M5N	
	M6	0699 132 606	834223/KQ2T06-M6N	
	R1/8	0699 133 106	834223/KQ2T06-01NS	
	R1/4	0699 133 206	834223/KQ2T06-02NS	
	R3/8	0699 133 306	834223/KQ2T06-03NS	
8	R1/8	0699 133 108	834223/KQ2T08-01NS	
	R1/4	0699 133 208	834223/KQ2T08-02NS	
	R3/8	0699 133 308	834223/KQ2T08-03NS	
10	R1/8	0699 133 110	834223/KQ2T10-01NS	
	R1/4	0699 133 210	834223/KQ2T10-02NS	
	R3/8	0699 133 310	834223/KQ2T10-03NS	
	R1/2	0699 133 410	834223/KQ2T10-04NS	
12	R1/4	0699 133 212	834223/KQ2T12-02NS	
	R3/8	0699 133 312	834223/KQ2T12-03NS	
	R1/2	0699 133 412	834223/KQ2T12-04NS	
16	R3/8	0699 133 316	834223/KQ2T16-03NS	
	R1/2	0699 133 416	834223/KQ2T16-04NS	
Ausführung		Messing	Messing/Nickel	5

\varnothing d mm	R	Art.-Nr.	Sonderbestellung-Nr.	VE/St.
6	R1/8	0699 145 106	834223/KQ2UD06-01NS	10
	R1/4	0699 145 206	834223/KQ2UD06-02NS	
Ausführung		Messing	Messing/Nickel	