

Klammer

Für Thermo Hefter WTG 40

Breite (b ₁)	15 mm
--------------------------	-------



Durchmesser (d ₁)	Länge (l ₁)	Form	Art.-Nr.	VE
0,6 mm	15 mm	U	0702 206 001	100
0,6 mm	16 mm	S	0702 206 002	100
0,7 mm	20 mm	M	0702 206 006	100
0,8 mm	15 mm	U	0702 206 003	100
0,8 mm	16 mm	S	0702 206 004	100
0,8 mm	21 mm	V	0702 206 005	100