

## BEFÜLLTE KOFFER SORTIMENTE 4.4.1



**5964 055 701**  
526 Teile

### ADERENDHÜLENS

Verzinkt, isoliert

| Art.-Nr.     | Grösse                         | VE/St. |
|--------------|--------------------------------|--------|
| 0557 004 00  | 4,0 mm <sup>2</sup> x 10,0 mm  | 50     |
| 0557 006 00  | 6,0 mm <sup>2</sup> x 12,0 mm  | 25     |
| 0557 010 00  | 10,0 mm <sup>2</sup> x 12,0 mm | 25     |
| 0557 016 00  | 16,0 mm <sup>2</sup> x 12,0 mm | 25     |
| 0557 000 50  | 0,5 mm <sup>2</sup> x 8,0 mm   | 100    |
| 0557 000 75  | 0,75 mm <sup>2</sup> x 8,0 mm  | 100    |
| 0557 001 00  | 1,0 mm <sup>2</sup> x 8,0 mm   | 100    |
| 0557 001 50  | 1,5 mm <sup>2</sup> x 8,0 mm   | 50     |
| 0557 300 251 | 2,5 mm <sup>2</sup> x 8,0 mm   | 50     |
| 0557 10      | Crimpzange                     | 1      |



**5964 062 500**  
155 Teile

### SPIRALBOHRER HSS

DIN 338 Typ N, 1,0–10,5 x 0,5 mm

| Art.-Nr. | Grösse                  | VE/St. |
|----------|-------------------------|--------|
| 0625 ..  | 1,0/1,5/2,0/2,5/3,0     | 10     |
| 0625 ..  | 3,5/4,0/4,5/5,0/5,5/6,0 | 10     |
| 0625 ..  | 6,5/7,0/7,5/8,0/8,5     | 5      |
| 0625 ..  | 9,0/9,5/10,0/10,5       | 5      |



**5964 062 600**  
73 Teile

### SPIRALBOHRER HSCO (5 % CO)

DIN 338

| Art.-Nr. | Grösse                  | VE/St. |
|----------|-------------------------|--------|
| 0626 ..  | 1,0/1,5/2,0/2,5/3,0     | 5      |
| 0626 ..  | 3,5/4,0/4,5/5,0/5,5/6,0 | 5      |
| 0626 ..  | 6,5/7,0/7,5/8,0/8,5     | 2      |
| 0626 ..  | 9,0/9,5/10,0/10,5       | 2      |



**5964 063 291**  
16 Teile

### HSSCO BI-METALL ZYLINDERSÄGEN

Von 19 – 76 mm, komplett mit Zubehör

| Art.-Nr.     | Grösse         | VE/St. |
|--------------|----------------|--------|
| 0632 900 0.. | 19/22/25/32 mm | 1      |
| 0632 900 0.. | 35/38/44/51 mm | 1      |
| 0632 900 0.. | 57/64/68/76 mm | 1      |
| 0632 05      | 300 mm         | 1      |
| 0632 02      | A2             | 1      |
| 0632 04 1    | A4             | 1      |
| 0632 07      | A7             | 1      |



**5964 063 292**  
13 Teile

### HSSCO BI-METALL ZYLINDERSÄGEN

Von 16 – 59 mm, komplett mit Zubehör

| Art.-Nr.     | Grösse      | VE/St. |
|--------------|-------------|--------|
| 0632 900 0.. | 16/19/21 mm | 1      |
| 0632 900 0.. | 22/29/37 mm | 1      |
| 0632 900 0.. | 48/54/59 mm | 1      |
| 0632 05      | 300 mm      | 1      |
| 0632 02      | A2          | 1      |
| 0632 04 1    | A4          | 1      |
| 0632 07      | A7          | 1      |



**5964 063 293**  
10 Teile

### HSSCO BI-METALL ZYLINDERSÄGEN

Von 22 – 67 mm, komplett mit Zubehör

| Art.-Nr.     | Grösse      | VE/St. |
|--------------|-------------|--------|
| 0632 900 0.. | 22/29/38 mm | 1      |
| 0632 900 0.. | 44/57/67 mm | 1      |
| 0632 05      | 300 mm      | 1      |
| 0632 02      | A2          | 1      |
| 0632 04 1    | A4          | 1      |
| 0632 07      | A7          | 1      |