

LASER DISTANCE METER WDM 3-19



Handy, lightweight and very precise distance meter for measuring lengths and calculating areas.

Measuring accuracy 1.5 mm over the complete measuring range of 0.2–100 metres.

Easy readability.
Large, illuminated 3-line display.

Shock protection.
Extra-thick soft elements.

Detects correct measuring position.
Fold-out measuring flap.

Data and images can be transmitted to a tablet or smartphone using the Android/iOS app.

Bluetooth smart function.

Automatic end detection.

No time-consuming pre-setting necessary.

Scope of delivery:

- 2 x 1.5 V AAA batteries
- Textile protective case
- Operating instructions on CD

Notice:

The WDM 3-19 meets the new ISO standard 1633-1.

| Description | Art. No. | P. Qty. |
|-------------------------------|---------------------|---------|
| Laser Distance Meter WDM 3-19 | 5709 300 523 | 1 |

| Technical Data | |
|--|--------------------------|
| Max. length measuring range | 100 m |
| Rechargeable battery/battery life | up to 10000 measurements |
| Number of rechargeable batteries/batteries | 2 PCS |
| Type of rechargeable battery/battery | Alkali |
| Length | 116 mm |
| Width | 53 mm |
| Height | 26 mm |
| Min./max. temperature conditions | -10 to 50 °C |
| Laser wavelength | 635 nm |
| IP protection class | IP 54 |
| Error of measurement for length (+/-) | +/- 1.5 mm |

