

MINI SANDING & GRINDING ASSORTMENT



The complete **Right Angle Die Grinder Assortment**. Contains all the necessary equipment needed for those small and hard to get to jobs in one handy system case.

Description	Art. No.	Pack Qty.
Mini Sanding & Grinding Assortment 19 Pieces	5964 070 301	1

Air Angle Die Grinder.

- Includes 1/4" and 6mm collets.
- Built-in regulator matches speed to the job.
- Safety throttle to prevent accidental start up.
- Free speed: 23,000rpm.
- Rugged, energy efficient 1/2 hp motor.

Mini Disc.

Flexible mini lamella fan-shaped grinding disc: Ø 50 mm with quick-action chuck for use with angled die grinders. Especially for stainless steel, chromium and nickel alloys, alloyed and unalloyed steels, construction steel, tool steel, non-ferrous metals, castings, hard plastics and wood.

Powerloc Fleece.

- Twist lock backing compatible with all backing pads.
- Ideal in confined spaces.
- High speed.
- Open flexible disc structure.

Fan Grinding Wheels.

For fine surface structures

- Aluminium-oxide.
- Synthetic resin-bonded grinding fabric.

Speed Cut Off disc.

For stainless steel alloys and high alloyed steels, rust and acid resistant steel, chromium-nickel steel.

Contents:

Description	Art. No.	Pack Qty.
Würth Air Die Grinder Right Angle	0703 231 014	1
Arbor for Cutting Wheels Bore 6.0mm	0664 975	
Würth Lock Disc Holder 50mm	0586 578 01	2
Nylon Power Loc 2" Brown Course	0673 205 010	
Nylon Power Loc 2" Maroon Medium	0673 205 018	
Nylon Power Loc 2" Blue Fine	0673 205 028	
Zebra Flexi Disc Zirc 50mm 40 Grit	0578 705 040	
Zebra Flexi Disc Zirc 50mm 80 Grit	0578 705 080	
Zebra Flexi Disc Zirc 50mm 120 Grit	0578 705 012	1
W-Fan Grinding Wheel 30x15x6 80 Grit	0672 010 318	
W-Fan Grinding Wheel 30x15x6 120 Grit	0672 010 311	
Speed Cut Off Disc S/Steel 50x1.0x6.0mm	0664 130 501	2