

RECHARGEABLE LED HEAD LAMP ERGOPOWER SENSOR



Compact headlamp, with sensor function.

Super bright light emitting surface 60° lighting.

Adjustable back bracket up and down within 60°.

Equipped with two switches:

- Standard on/off switch - 1. step half light intensity, 2. step full light intensity.
- Sensor switch - motion sensor (with hand movements) up to 5 cm distance to the lamp.

Protection class IP65.

Impact resistance IK07.

Headband with integrated anti-slip rubber strip.

Provides better grip.

Min./Max. Luminous Flux	Min./max. luminous period	Charging Time	IP Protection Class	Art. No.	Pack Qty.
100/280 lm	5.5 - 2 h	2.5 h	IP 65	0827 809 635	1

Notice:

Supplied with Micro USB.

RECHARGEABLE PEN LIGHT LED



6 + 1 LED Small pen light with magnet and clip.

Latest lithium-polymer battery technology.

Short charging time, long light duration

Features:

- Main light with 6 SMD LED.
- Spot light at the bottom.
- Switch mode - spot light, main light, off.
- Battery charging status by indicator light.
- Power supply and USB cable included in the delivery.

Technical Data:

Min. colour rendering index (CRI)	70
Luminous period	3 h
Charging time	2.5 h (Charged by 5VDC/1A Adapter)
IP protection class	IP 20
Nominal voltage	5 V/DC
Rechargeable battery/battery capacity	800 mAh
Art. No.	0827 500 022
P. Qty.	1
Included	Lamp, Micro USB cable and AC Adapter



Accessories	Art. No.	P. Qty
240V Charger	0827 940 375	1
Mini USB Cable	0827 940 374	
Car Charger	0827 940 373	