



Matière : Finition chromée polie.

⌀ mm	L1 mm	D1 mm	D2 mm	t mm	Art. N°	Condit.
4,0	22	6,8	11,1	2,6	0713 111 104	1
5,0	22	8,2	11,1	4,6	0713 111 105	1
5,5	22	8,7	11,1	4,8	0713 111 155	1
6,0	22	9,3	11,1	5,4	0713 111 106	1
7,0	22	10,8	10,8	5,8	0713 111 107	1
8,0	22	11,9	11,9	6,4	0713 111 108	1
9,0	22	13,0	13,0	6,4	0713 111 109	1
10,0	22	14,6	14,6	7,5	0713 111 110	1
11,0	22	15,7	15,7	8,6	0713 111 111	1
12,0	22	16,9	16,9	9,3	0713 111 112	1
13,0	22	17,6	17,6	9,8	0713 111 113	1
14,0	22	18,6	18,6	10,0	0713 111 114	1

Douille 1/4" métrique

Caractéristique :

- Exécution courte.



▼ Cliquet 1/4"