

TAPPETINO IN GOMMA ANTISCIVOLO

descrizione	largh.	lungh.	spess.	peso	Art.
MAM59	306 mm	1345 mm	3 mm	0,398 kg	0963 580 159
MAM60	190 mm	1650 mm	3 mm	0,303 kg	0963 580 160
MAM61	325 mm	831 mm	3 mm	0,261 kg	0963 580 161
MAM62	325 mm	1108 mm	3 mm	0,348 kg	0963 580 162
MAM63	325 mm	1387 mm	3 mm	0,436 kg	0963 580 163
MAM64	325 mm	1665 mm	3 mm	0,523 kg	0963 580 164
MAM65	306 mm	791 mm	3 mm	0,234 kg	0963 580 165
MAM66	306 mm	1070 mm	3 mm	0,317 kg	0963 580 166
MAM67	270 mm	1310 mm	3 mm	0,342 kg	0963 580 167
MAM68	270 mm	1010 mm	3 mm	0,264 kg	0963 580 168
MAM69	1000 mm	5000 mm	3 mm	4,834 kg	0963 580 169
MAM70	190 mm	3050 mm	3 mm	0,56 kg	0963 580 170
MAM71	270 mm	730 mm	3 mm	0,191 kg	0963 580 171
MAM72	266 mm	514 mm	3 mm	0,132 kg	0963 580 172
MAM73	266 mm	1069 mm	3 mm	0,275 kg	0963 580 173
MAM74	262 mm	1345 mm	3 mm	0,341 kg	0963 580 174
MAM75	260 mm	3050 mm	3 mm	0,767 kg	0963 580 175
MAM76	346 mm	548 mm	3 mm	0,183 kg	0963 580 176
MAM77	416 mm	547 mm	3 mm	0,22 kg	0963 580 177
MAM79	287 mm	755 mm	3 mm	0,21 kg	0963 580 179
MAM80	340 mm	754 mm	3 mm	0,248 kg	0963 580 180
MAM81	409 mm	755 mm	3 mm	0,299 kg	0963 580 181
MAM82	302 mm	479 mm	3 mm	0,14 kg	0963 580 182
MAM87	272 mm	350 mm	3 mm	0,092 kg	0963 580 187
MAM88	358 mm	553 mm	3 mm	0,191 kg	0963 580 188
MAM89	428 mm	552 mm	3 mm	0,228 kg	0963 580 189
MAM90	378 mm	553 mm	3 mm	0,202 kg	0963 580 190
MAM91	428 mm	1109 mm	3 mm	0,459 kg	0963 580 191
MAM92	428 mm	1386 mm	3 mm	0,574 kg	0963 580 192
MAM93	358 mm	1109 mm	3 mm	0,384 kg	0963 580 193
MAM95	244 mm	1109 mm	3 mm	0,262 kg	0963 580 195
MAM97	428 mm	831 mm	3 mm	0,344 kg	0963 580 197
MAM98	358 mm	832 mm	3 mm	0,288 kg	0963 580 198
MAM99	244 mm	831 mm	3 mm	0,196 kg	0963 580 199
MAM100	358 mm	1387 mm	3 mm	0,48 kg	0963 580 100
MAM102	306 mm	1109 mm	3 mm	0,328 kg	0963 580 102
MAM103	306 mm	1387 mm	3 mm	0,41 kg	0963 580 103
MAM201	235 mm	358 mm	3 mm	0,081 kg	0963 580 201
MAM202	235 mm	306 mm	3 mm	0,07 kg	0963 580 202
MAM203	235 mm	248 mm	3 mm	0,056 kg	0963 580 203
MAM204	232 mm	376 mm	3 mm	0,084 kg	0963 580 204
MAM205	232 mm	324 mm	3 mm	0,073 kg	0963 580 205
MAM206	232 mm	262 mm	3 mm	0,059 kg	0963 580 206
MAM207	305 mm	1347 mm	3 mm	0,4 kg	0963 580 207
MAM208	305 mm	1069 mm	3 mm	0,38 kg	0963 580 208
MAM209	305 mm	790 mm	3 mm	0,32 kg	0963 580 209