

INSERTI AW

Assy® 0170 ... 0153 ... 0154 ...	Assy® A2 0180 ... Ecofast Assy® 0165 ... 0166 ...	Isotop Assy® 0164 ... Assy® SK Assy® Kombi 0184 ...	AMO® III 0234 ... Jamo® 0234 ... viti ancoranti tipo D e F 0233 ...	ZEBRA pias® 0205 ... 0206 ...	autofilettanti 0111 ... 0112 .. 0113 ... 0127 ...	Assy® 3.0 SK 0184 8... Assy® plus VG 0165 ...	AW®
Ø filetto	Ø filetto	Ø filetto	Ø filetto	Ø filetto	Ø filetto	Ø filetto	
3,0				2,9 3,5	2,9 3,5		AW10
3,5 4,0 4,5 5,0	3,5 4,0 4,5 5,0			3,9 4,2	3,9 4,2		AW20
				4,8 5,5	4,8 5,5		AW25
6,0 7,0	6,0 7,0	6,0	6,0 7,0 7,5	6,3			AW30
8,0 10,0 12,0	8,0 10,0 12,0	8,0		8,0			AW40
						10,0 12,0	AW50

AW®	1/4"	5/16"	1/4"	1/4"	1/4"	7 mm	M4	M5	M5	M6	M6	
	25 mm	32 mm	50 mm	70 mm	110 mm	53 mm	45 mm	33 mm	45 mm	33 mm	45 mm	
	0614 ...	0614 ...	0614 ...	0614 ...	0614 ...	0614 ...	0614 ...	0614 ...	0614 ...	0614 ...	0614 ...	0614 ...
AW10	511 0	—	521 0	—	581 0	531 0	441 0	561 0	541 0	—	—	—
AW20	512 0	552 0	522 0	572 0	582 0	532 0	—	562 0	542 0	612 0	622 0	—
AW25	512 5	552 5	522 5	—	582 5	532 5	—	562 5	—	612 5	622 5	—
AW30	513 0	553 0	523 0	573 0	583 0	—	—	—	—	—	—	—
AW40	514 0	554 0	524 0	574 0	—	—	—	—	—	—	—	—
AW50	—	550 50*	—	—	—	—	—	—	—	—	—	—

* lunghezza 50 mm