


VITE PER CARPENTERIA WÜPOFAST II TX

| diametro nominale d [mm] | lunghezza l [mm] | lunghezza filetto lg [mm] | diametro testa dh [mm] | altezza testa k [mm] | impronta TX  | Art. |
|--------------------------|---------------------|---------------------------|------------------------|----------------------|---|---------------------|
| 8 | 80 | 50 | 14,7 | 7 | TX 40 | 0176 018 80 |
| | 100 | 60 | | | | 0176 018 100 |
| | 120 | 80 | | | | 0176 018 120 |
| | 140 | | | | | 0176 018 140 |
| | 160 | | | | | 0176 018 160 |
| | 180 | | | | | 0176 018 180 |
| | 200 | | | | | 0176 018 200 |
| | 220 | | | | | 0176 018 220 |
| | 240 | 100 | | | | 0176 018 240 |
| | 260 | | | | | 0176 018 260 |
| | 280 | | | | | 0176 018 280 |
| | 300 | | | | | 0176 018 300 |
| | 320 | | | | | 0176 018 320 |
| | 340 | | | | | 0176 018 340 |
| | 360 | | | | | 0176 018 360 |
| | 380 | | | | | 0176 018 380 |
| 400 | 0176 018 400 | | | | | |
| 10 | 120 | 80 | 18,2 | 9 | TX 40 | 0176 010 120 |
| | 140 | 100 | | | | 0176 010 140 |
| | 160 | | | | | 0176 010 160 |
| | 180 | | | | | 0176 010 180 |
| | 200 | | | | | 0176 010 200 |
| | 220 | | | | | 0176 010 220 |
| | 240 | | | | | 0176 010 240 |
| | 260 | 120 | | | | 0176 010 260 |
| | 280 | | | | | 0176 010 280 |
| | 300 | | | | | 0176 010 300 |
| | 320 | | | | | 0176 010 320 |
| | 340 | | | | | 0176 010 340 |
| | 360 | | | | | 0176 010 360 |
| | 380 | | | | | 0176 010 380 |
| 400 | 0176 010 400 | | | | | |

Articoli aggiuntivi: inserti TX

| misura | colore | Art. |
|--------|--------|-------------------|
| TX20 | | 0614 312 0 |
| TX30 | | 0614 313 0 |
| TX40 | | 0614 314 0 |