

ASSY® PLUS 4 VG CH

TESTA CILINDRICA, FI, RW, ACCIAIO ZINC.BIANCO

diametro nominale d [mm]	lunghezza l [mm]	lunghezza filetto lg [mm]	lunghezza filetto con punta b [mm]	diametro testa dh [mm]	altezza testa k [mm]	impronta RW	Art.
6	80	67	67	8,2	4,7	RW30	0150 006 080
	100	87	87				0150 006 100
	120	107	107				0150 006 120
	140	123	123				0150 006 140
	160	143	143				0150 006 160
	180	163	163				0150 006 180
	200	183	183				0150 006 200
	220	203	203				0150 006 220
	240	223	223				0150 006 240
	260	243	243				0150 006 260
8	120	101	101	10	7,5	RW40	0150 008 120
	140	121	121				0150 008 140
	160	141	141				0150 008 160
	180	161	161				0150 008 180
	200	181	181				0150 008 200
	220	201	201				0150 008 220
	240	221	221				0150 008 240
	260	241	241				0150 008 260
	280	261	261				0150 008 280
	300	275	275				0150 008 300
	330	305	305				0150 008 330
	340	315	315				0150 008 340
	360	335	335				0150 008 360
	380	355	355				0150 008 380
	400	375	375				0150 008 400
	430	405	405				0150 008 430
	450	425	425				0150 008 450
	480	445	445				0150 008 480
530	495	495	0150 008 530				
580	545	545	0150 008 580				
10	120	97	97	13,4	8	RW50	0150 010 120
	140	117	117				0150 010 140
	160	137	137				0150 010 160
	180	157	157				0150 010 180
	200	177	177				0150 010 200
	220	197	197				0150 010 220
	240	217	217				0150 010 240
	260	237	237				0150 010 260
	280	257	257				0150 010 280
	300	272	272				0150 010 300
	320	292	292				0150 010 320
	340	312	312				0150 010 340
	360	332	332				0150 010 360
	380	352	352				0150 010 380
	400	372	372				0150 010 400
	430	402	402				0150 010 430
	450	422	422				0150 010 450
	480	442	442				0150 010 480