





TASSELLO PROLUNGATO IN NYLON SHARK® UR 10

vite	materiale	tassello Ø x L _t [mm]	vite Ø _v x L _v [mm]	f _{fix} (per h _{nom} = 70 mm)	Art.
 TPS Ø testa: 14 mm intaglio AW40	zincato bianco	10 x 80	7 x 85	10	5912 810 401
		10 x 100	7 x 105	30	5912 810 402
		10 x 115	7 x 120	45	5912 810 403
		10 x 135	7 x 140	65	5912 810 404
		10 x 160	7 x 165	90	5912 810 405
		10 x 185	7 x 190	115	5912 810 406
		10 x 200	7 x 205	130	5912 810 407
		10 x 230	7 x 235	160	5912 810 408
		10 x 260	7 x 265	190	5912 810 409
		10 x 290	7 x 295	220	5912 810 410
10 x 320	7 x 325	250	5912 810 411		
 TPS Ø testa: 14 mm intaglio AW40	inox A4	10 x 80	7 x 85	10	5912 810 501
		10 x 100	7 x 105	30	5912 810 502
		10 x 115	7 x 120	45	5912 810 503
		10 x 135	7 x 140	65	5912 810 504
		10 x 160	7 x 165	90	5912 810 505
		10 x 185	7 x 190	115	5912 810 506
		10 x 200	7 x 205	130	5912 810 507
 TE Ø testa: 19 mm intaglio AW40 chiave 13	zincato bianco	10 x 80	7 x 85	10	5912 810 601
		10 x 100	7 x 105	30	5912 810 602
		10 x 115	7 x 120	45	5912 810 603
		10 x 135	7 x 140	65	5912 810 604
		10 x 160	7 x 165	90	5912 810 605
		10 x 185	7 x 190	115	5912 810 606
		10 x 200	7 x 205	130	5912 810 607
10 x 230	7 x 235	160	5912 810 608		
 TE Ø testa: 19 mm chiave 13	inox A4	10 x 80	7 x 85	10	5912 810 701
		10 x 100	7 x 105	30	5912 810 702
		10 x 115	7 x 120	45	5912 810 703
		10 x 135	7 x 140	65	5912 810 704
		10 x 160	7 x 165	90	5912 810 705

