

▲ 1000 V



VDE binnenzeskant-schroevendraaier

Kling: gebruind, geïsoleerd
 Uitvoering: DIN 911
 Norm: DIN 7439, IEC 900, EN 60900

mm	A B C		A Inch	Art.nr	Verp.
	A mm	B/C mm			
2,5	80	83/27	3 1/8"	0613 635 025	1
3,0	80	83/27	3 1/8"	0613 635 03	
4,0	80	96/31	3 1/8"	0613 635 04	
5,0	80	106/35	3 1/8"	0613 635 05	
6,0	100	106/35	4"	0613 635 06	
8,0	100	114/38	4"	0613 635 08	



Schroevendraaierset

Voor elektronisch handwerk
 Volgens DIN 7437/7438, IEC 900, EN 60900.

Art.nr 0613 963 25

	Art.nr		Art.nr.	Verp.
0,4 x 2,5 x 80	0613 631 025	H1	0613 632 1	1
0,8 x 4,0 x 100	0613 631 04	H2	0613 632 2	
1,2 x 6,5 x 150	0613 631 065			



Art.nr 0613 963 35

	Art.nr		Art.nr.	Verp.
0,4 x 2,5 x 80	0613 631 025	Z1	0613 633 1	1
0,8 x 4,0 x 100	0613 631 04	Z2	0613 633 2	
1,2 x 6,5 x 150	0613 631 065			