

Menovitý Ø d mm	Délka l mm	Oceľ pozink. namodro Obj.č.	Bal./ks	A2 Obj.č.	Bal./ks
4,8	9,5	116 48 95	100		
	13	116 48 13	100/1000	123 48 13	300/1000
	16	116 48 16	300/1000	123 48 16	
	19	116 48 19	100/1000	123 48 19	
	22	116 48 22		123 48 22	100/1000
	25	116 48 25		123 48 25	
	32	116 48 32		123 48 32	
	38	116 48 38	100/500	123 48 38	100/500
	45	116 48 45		123 48 45	
	50	116 48 50		123 48 50	
	55		123 48 55		
	60	116 48 60	100	123 48 60	
	70	116 48 70	100/500	123 48 70	
	80	116 48 80	100	123 48 80	100
	90	116 48 90		123 48 90	
	100	116 48 100		123 48 100	
110	116 48 110				
120	116 48 120				
5,5	13	116 55 13	100	123 55 13	100
	16	116 55 16		123 55 16	
	19	116 55 19		123 55 19	
	22	116 55 22		123 55 22	
	25	116 55 25		123 55 25	
	32	116 55 32	100/500	123 55 32	100/500
	38	116 55 38		123 55 38	
	45	116 55 45	100	123 55 45	100
	50	116 55 50		123 55 50	
	60	116 55 60		123 55 60	
	70	116 55 70		123 55 70	
	80	116 55 80		123 55 80	
	90	116 55 90		123 55 90	
	100	116 55 100		123 55 100	
110	116 55 110				
120	116 55 120		123 55 120		
6,3	16	116 63 16	100	123 63 16	100
	19	116 63 19		123 63 19	
	22	116 63 22			
	25	116 63 25		123 63 25	
	32	116 63 32	100/500	123 63 32	
	38	116 63 38		123 63 38	
	45	116 63 45		123 63 45	
	50	116 63 50	100	123 63 50	
	60	116 63 60		123 63 60	
	70	116 63 70		123 63 70	
	80	116 63 80		123 63 80	
	90	116 63 90		123 63 90	
	100	116 63 100		123 63 100	
	110	116 63 110			
120	116 63 120				