

## 1/2" zakladacie kľúče 6-hranné, metrické


Norma: DIN 3124, ISO 2725.

Vyhotovenie: s pochrómovaným  
povrchom, brúsené/matné.

Otvor: 1/2", s drážkou pre poistnú guľku.

Výstup: 6-hran, metrický, Powerdriv.

Geometria: krátky.



mm	L1 mm	D1 mm	D2 mm	t mm	Obj.č.	
8	36	13	23	8	712 131 108	1/10
9	36	14,2	23	9	712 131 109	
10	36	15,5	23	9	712 131 110	
11	36	16,7	23	10	712 131 111	
12	36	18	23	11	712 131 112	
13	36	19,2	23	11	712 131 113	
14	36	20,5	23	13	712 131 114	
15	36	21,7	22	13	712 131 115	
16	36	23	23,2	13	712 131 116	
17	36	24,2	23,2	13	712 131 117	
18	36	25,5	23,5	14	712 131 118	
19	36	26,7	24,7	14	712 131 119	
20	36	28	25,5	14	712 131 120	
21	38	29,2	26	14	712 131 121	
22	38	30,5	26,5	16	712 131 122	
23	38	31,7	27,7	16	712 131 123	
24	38	33	29	18	712 131 124	
26	38	35,5	31,5	18	712 131 126	
27	44	36,7	32,2	20	712 131 127	
28	44	38	33,5	20	712 131 128	
30	44	40,5	36	22	712 131 130	
32	44	43	38,1	24	712 131 132	
34	47	45,5	40	25	712 131 134	

## 1/2" zakladacie kľúče 12-hranné, metrické


Norma: DIN 3124, ISO 2725.

Vyhotovenie: s pochrómovaným  
povrchom, brúsené/matné.

Otvor: 1/2", s drážkou pre poistnú guľku.

Výstup: 12-hran, metrický, Powerdriv.

Geometria: krátky.



mm	L1 mm	D1 mm	D2 mm	t mm	Obj.č.	
8	36	12,9	21,9	7	712 133 108	1/10
9	36	14	21,9	8	712 133 109	
10	36	15,4	21,9	10	712 133 110	
11	36	16,6	21,9	10	712 133 111	
12	36	17,9	21,9	10	712 133 112	
13	36	19,1	21,9	11	712 133 113	
14	36	20,4	21,9	11	712 133 114	
15	36	21	21,9	11	712 133 115	
16	36	22,5	21,9	11	712 133 116	
17	36	24	23,2	11	712 133 117	
18	36	25,4	23,5	16	712 133 118	
19	36	26,5	24,7	16	712 133 119	
20	36	27,9	25,5	16	712 133 120	
21	38	28,5	26	19	712 133 121	
22	38	29,9	26,5	19	712 133 122	
23	38	31,2	27,7	19	712 133 123	
24	38	32	29	19	712 133 124	
26	38	35	31,5	19	712 133 126	
27	44	36	32,2	24	712 133 127	
28	44	37,7	33,5	24	712 133 128	
30	44	40	36	24	712 133 130	
32	44	42	38,1	24	712 133 132	
34	47	45	40	27	712 133 134	