

SADY V SYSTÉM. KUFRÍKOCH 4.4.1 - KRÚŽKY



5964 046 220
585 dielov

MEDENÉ TESNIACE KRÚŽKY

Obj.č.	Popis/rozmery	Bal./ks
0462 0...	10 x 14 / 12 x 16 / 14 x 20 mm	50
0462 0...	14 x 22 / 16 x 20 / 16 x 22 mm	30
0462 0...	18 x 22 / 18 x 24 / 20 x 26 mm	25
0462 0...	22 x 27 / 24 x 30 / 26 x 32 mm	25
0462 0...	28 x 34 / 30 x 38 / 32 x 38 mm	15
0462 0...	5 x 9 / 6 x 20 / 8 x 12 mm	50



5964 046 300
525 dielov

TESNIACE KRÚŽKY DIN 7603 A

Hliník

Obj.č.	Popis/rozmery	Bal./ks
0463 6 10	6 x 10	50
0463 8 ...	8 x 12/8 x 14	50
0463 10 ...	10 x 14/10 x 16	25
0463 12 ...	12 x 16/12 x 18	25
0463 14 ...	14 x 18/14 x 20	25
0463 16 ...	16 x 20/16 x 22	25
0463 18 ...	18 x 22/18 x 24	25
0463 20 26	20 x 26	25
0463 22 27	22 x 27	25
0463 24 30	24 x 30	25
0463 26 32	26 x 32	25
0463 30 36	30 x 36	25



5964 046 500
1170 dielov

TESNIACE KRÚŽKY DIN 7603 A

Vulkanizovaný fiber

Obj.č.	Popis/rozmery	Bal./ks
0465 5 9	5 x 9	100
0465 ...	6 x 10/8 x 12/8 x 14	100
0465 ...	10 x 14/10 x 16/12 x 16	100
0465 ...	14 x 18/16 x 22/18 x 24	50
0465 ...	20 x 26/22 x 27	50
0465 ...	24 x 30/26 x 32	30
0465 ...	28 x 34/30 x 36	25
0465 122 19	12,2 x 19	70
0465 142 24	14,2 x 24	40



5964 046 800
1050 dielov

O-KRÚŽKY, METRICKÉ ROZMERY

Ø 3,0 mm - Ø 24,0 mm

Obj.č.	Popis/rozmery	Bal./ks
0468 00...	Ø 3,0 x 2,0/Ø 4,0 x 2,0	100
0468 00...	Ø 5,0 x 2,0/Ø 6,0 x 2,0	100
0468 00...	Ø 7,0 x 2,0/Ø 8,0 x 2,0	100
0468 01...	Ø 10,0 x 2,0/Ø 12,0 x 2,0	50
0468 01...	Ø 10,0 x 2,5/Ø 12,0 x 2,5	50
0468 01...	Ø 14,0 x 2,5/Ø 15,0 x 2,5	50
0468 01...	Ø 17,0 x 2,5/Ø 19,0 x 2,5	25
0468 018 30	Ø 18,0 x 3,0	25
0468 02...	Ø 20,0 x 3,0/Ø 22,0 x 3,0	25
0468 024 30	Ø 24,0 x 3,0	25



5964 046 801
440 dielov

O-KRÚŽKY PERBUNAN, PALCOVÉ ROZMERY

Ø 5,28 mm - Ø 36,10 mm

Obj.č.	Popis/rozmery	Bal./ks
0468 ...	Ø 5,28 x 1,78/Ø 6,07 x 1,78	50
0468 ...	Ø 7,66 x 1,78/Ø 9,25 x 1,78	50
0468 ...	Ø 10,78 x 2,62/Ø 12,37 x 2,62	30
0468 ...	Ø 13,95 x 2,62/Ø 15,54 x 2,62	30
0468 ...	Ø 17,13 x 2,62/Ø 18,72 x 2,62	20
0468 202 2	Ø 20,22 x 3,53	20
0468 ...	Ø 23,40 x 3,53/Ø 25,00 x 3,53	15
0468 ...	Ø 26,57 x 3,53/Ø 28,17 x 3,53	15
0468 ...	Ø 31,34 x 3,53/Ø 34,52 x 3,53	10
0468 361 0	Ø 36,10 x 3,53	10



5964 046 802
330 dielov

O-KRÚŽKY PERBUNAN, METRICKÉ ROZMERY

Ø 25,0 mm - Ø 42,0 mm

Obj.č.	Popis/rozmery	Bal./ks
0468 025 30	Ø 25,0 x 3,0	50
0468 028 30	Ø 28,0 x 3,0	50
0468 030 30	Ø 30,0 x 3,0	50
0468 034 30	Ø 34,0 x 3,0	25
0468 036 30	Ø 36,0 x 3,0	25
0468 038 30	Ø 38,0 x 3,0	25
0468 040 30	Ø 40,0 x 3,0	25
0468 042 30	Ø 42,0 x 3,0	25
0468 030 35	Ø 30,0 x 3,5	25
0468 032 35	Ø 32,0 x 3,5	10
0468 033 35	Ø 33,0 x 3,5	10
0468 035 35	Ø 35,0 x 3,5	10