

SKRUTKOVAČ VDE, PRE VNÚTORNÝ 6-HRAN




Na prácu s dielmi pod napätím až 1000 V (AC) a až 1500 V (DC)

- Čepel: brunírovaná, izolovaná
- Hrot: DIN 911
- Norma: DIN 7439, IEC 900, EN 60900

	A mm	B/C mm	A palce	Obj.č.	Bal./ks
2.5	80	83/27	3 1/8"	0613 635 025	1
3.0	80	83/27	3 1/8"	0613 635 03	1
4.0	80	96/31	3 1/8"	0613 635 04	1
5.0	80	106/35	3 1/8"	0613 635 05	1
6.0	100	106/35	4"	0613 635 06	1
8.0	100	114/38	4"	0613 635 08	1

SKRUTKOVAČ VDE, PRE VONKAJŠÍ 6-HRAN



Na prácu s dielmi pod napätím až 1000 V (AC) a až 1500 V (DC)

- Čepel: brunírovaná, izolovaná
- Hrot: DIN ISO 691
- Norma: IEC 60900:2012

	A mm	B/C mm	A palce	Obj.č.	Bal./ks
5,5	125	96/31	5"	0613 636 055	1
6,0	125	96/31	5"	0613 636 06	1
7,0	125	106/35	5"	0613 636 07	1
8,0	125	106/35	5"	0613 636 08	1
9,0	125	106/35	5"	0613 636 09	1
10,0	125	106/35	5"	0613 636 10	1
11,0	125	114/38	5"	0613 636 11	1
12,0	125	114/38	5"	0613 636 12	1
13,0	125	114/38	5"	0613 636 13	1

	A mm	Obj.č.		A mm	Obj.č.	Bal./ks
5,5	125	0613 636 055	8,0	125	0613 636 08	1
6,0	125	0613 636 06	10,0	125	0613 636 10	1
7,0	125	0613 636 07	13,0	125	0613 636 13	1

Sada skrutkovačov VDE,
pre vonkajší 6-hran
Obj.č. 0613 936 66

